



BIBS3506MT, Mount, 6-Cond. Clear Ins. MultiTap

By Burndy
Catalog # [BIBS3506MT](#)



#10 AWG - 350 kcmil, 6 Ports, Single-sided Entry, Al/Cu Rated, Mountable, Clear Plastisol allows visual confirmation conductor is properly inserted

Features

- Clear Plastisol covered AL6061-T6 aluminum body saves times and lowers installation costs and eliminates taping
- Clear plastisol allows visual confirmation that conductor is properly inserted
- Oxide inhibitor pre-installed inhibits moisture and contaminants from entering the contact area
- Range-taking capability reduces number of connectors necessary to carry in inventory

Specifications

Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Certification - ETL	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
Certification - UL Listed Direct Burial	No
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - AL Str Size Range	10 AWG - 350 kcmil
Conductor Size	10 AWG-350 KCMIL
Conductor Type	• AL C Str-Size • CU C Str-Size
Conductor - Copper Str Size Range	10 AWG - 350 kcmil

Configuration

Physical Attribute - Number of Screws	8
Number Of Ports	6
Connector Type	Multi Tap

Current

Voltage - Maximum	600 V
-------------------	-------

Package Height	0.000 in
Dimension - Height mm	67 mm
Dimension - Height inch	2.63 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	195 mm
Width	2.19 in
Length	7.68 in
Dimension - Width mm	56 mm
Dimension - Width inch	2.19 in
Height	2.63 in
Dimension - Length Overall inch	7.68 in
Dimensions	7.68 in x 2.19 in x 2.63 in

General

Insulation Type	Plastisol
Trade Name	UNITAP™
Insulation	Y
Physical Attribute - Screw Type	Allen
Plated	N
UPC	781810253120
Hex Key	5/16
Material	Aluminum
Plating Type	Unplated
UPC 12 Digit	781810253120
UPC 14 Digit GTIN	00781810253120

Logistics

Minimum Pack Quantity	5
Pallet Quantity	1008
Carton Quantity	42

Operational

Temperature Rating	194
--------------------	-----

Product Assets

[Catalog \[English\]](#)
[Catalog \[English\]](#)

Dimensions



A Hubbell brand