



BGBL1/0, Tin Plated Aluminum Lay-in Lug, 1/0-14 AWG

By Burndy
Catalog # [BGBL1/0](#)

Tin Plated Aluminum Lay-in Lug, 1/0-14 AWG, 3/8" Zinc Plated Terminal Screw, 1/4" Stud



Features

- UL486B Listed, AL9CU Rated for copper and aluminum conductor combinations up to 90°C
- UL Recognized for grounding and bonding
- Lay-in feature eases installation

Application

For Copper And Aluminum Conductor Combinations Up To 90 DEG C

Specifications

Buy American Compliant	No
Industry Standard(s)	UL 486A-B
Standards - Industry Standards Met	UL 486A-B
Standards - RoHS Compliance	CM
Status	
Certification - UL Listed Direct Burial	No
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - AL Str Size	• 8 AWG • 6 AWG • 4 AWG • 3 AWG • 2 AWG • 1 AWG • 1/0 AWG
Conductor - AL Str Size Range	8 AWG-1/0 AWG
Conductor - Copper Str Size	• 14 AWG • 12 AWG • 10 AWG • 9 AWG • 8 AWG • 7 AWG • 6 AWG • 5 AWG • 4 AWG • 3 AWG • 2 AWG • 1 AWG • 1/0
Conductor - Copper Solid Size	• 14 AWG • 13 AWG • 12 AWG

Conductor - Copper Solid Size Range	• 11 AWG • 10 AWG • 9 AWG • 8 AWG • 7 AWG • 6 AWG • 5 AWG • 4 AWG • 3 AWG • 2 AWG • 1 AWG • 1/0 AWG
Conductor Type	• AL C Str-Size • CU C Str-Size • CU C Solid-Size
Conductor - Copper Str Size Range	14 AWG - 1/0 AWG

Dimensions

Dimension - Pad Width inch	0.60 in
Package Height	0.000 in
Dimension - Height mm	29.7 mm
Dimension - Height inch	1.17 in
Dimension - Height fraction	1-1/6 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	38 mm
Dimension - Hole Size mm	7 mm
Dimension - Hole Size inch	0.28 in
Dimension - D inch	0.80 in
Dimension - N inch	0.3 in
Dimension - Length Overall inch	1.50 in
Hex Size	Slot

Force Related

Installation Torque Recommended in-lb	50 LBS/in
---------------------------------------	-----------

General

Trade Name	QIKLUG™
Material Type - Screw	Steel - Zinc Plated
Physical Attribute - Screw Type	Slot
Plated	Yes
Sub Brand	QIKLUG

Product Type	Mechanical	Minimum Pack Quantity	1
UPC	781810124840	Pallet Quantity	1
Type	BGBL, Lay-In	Carton Quantity	600
Material	Aluminum		
Plating Type	Tin		
UPC 12 Digit	781810124840		
UPC 14 Digit GTIN	00781810124840		

Operational

Temperature Rating	194
--------------------	-----

Product Assets

Logistics

[Catalog \[English\]](#)



A Hubbell brand