



C11D, Bronze Ground Clamp, Cable to Water Pipe/Tube/Rebar

By Burndy
Catalog # C11D

Cast Bronze Ground Clamp, Cable to Water Pipe or Copper Tube,
10 - 2 AWG, 1/2"- 1" Water Pipe, #4 - #8 Rebar

Features

- Connects grounding conductor to water pipe or copper tube
- D indicates UL467 Listed for Direct Burial in earth and concrete
- Supplied with silicon bronze hardware

Application

For Bare Wire, Connecting Grounding Conductor To Water Pipe Or Copper Tube, Direct Burial Applications In Earth And Concrete

Specifications

Certification - UL Recognized	No
Certification - cULus	No
EU RoHS Indicator	Yes
Industry Standard(s)	UL467
Certification - ETL	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance	NC
Status	
Certification - UL Listed Direct Burial	Yes
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor - Rebar Size	• 4 • 5 • 6 • 7 • 8
Conductor - Rebar Size Range	4 -8
Conductor - Pipe EMT Size Range	1/2 in-1 in
Conductor - Pipe EMT Size	• 1/2 in • 3/4 in • 1 in
Conductor - Copper Str Size	• 10 AWG • 9 AWG • 8 AWG • 7 AWG • 6 AWG • 5 AWG • 4 AWG



Conductor - Copper Solid Size	• 3 AWG • 2 AWG • 10 AWG • 9 AWG • 8 AWG • 7 AWG • 6 AWG • 5 AWG • 4 AWG • 3 AWG • 2 AWG
Conductor - Armored Cable Size	N
Conductor - Copper Solid Size Range	10 AWG-2 AWG
Conductor - Copper Str Size Range	10 AWG - 2 AWG

Dimensions

Dimension - Pad Width inch	0.63 in
Package Height	0.000 in
Dimension - Height mm	46 mm
Dimension - Height inch	1.81 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	57 mm
Dimension - Hole Size mm	8 mm
Dimension - Hole Size inch	0.31 in
Dimension - Width mm	16 mm
Dimension - Width inch	0.63 in
Dimension - Length Overall inch	2.25 in

General

Material - Hardware	DURIUM™ Silicon Bronze
Plated	N
Sub Brand	CLAMP
UPC	781810142349
Type	Ground Clamp
Material	Bronze Alloy
Plating Type	Unplated
UPC 12 Digit	781810142349
UPC 14 Digit GTIN	00781810142349

Logistics

Pallet Quantity	10000
Carton Quantity	100

Product Assets

[Catalog \[English\]](#)



A Hubbell brand