



## C22, Cast Bronze Ground Clamp, Cable to Pipe or Tube

By Burndy  
Catalog # [C22](#)

Cast Bronze Ground Clamp, Cable to Water Pipe or Copper Tube, 10 - 2 AWG, 1-1/4" - 2" Water Pipe

### Features

- Connects grounding conductor to water pipe or copper tube
- Supplied with Zinc-plated steel hardware

### Application

For Bare Wire, Connecting Grounding Conductor To Water Pipe Or Copper Tube

### Specifications

|                                    |                      |
|------------------------------------|----------------------|
| Certification - UL Recognized      | No                   |
| Buy American Compliant             | Contact Manufacturer |
| Certification - cULus              | No                   |
| Buy America(n) Qualified           | Contact Manufacturer |
| Industry Standard(s)               | UL467                |
| Certification - ETL                | No                   |
| Standards - Industry Standards Met | UL467                |
| Standards - RoHS Compliance        | NC                   |
| Status                             |                      |
| Certification - UL Listed Direct   | No                   |
| Burial                             |                      |
| UL Listed                          | Yes                  |
| Certification - CSA Approved       | No                   |

### Conductor

|                                 |                                                                                                                                                                                          |
|---------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Conductor - Pipe EMT Size Range | 1 1/4 in-2 in                                                                                                                                                                            |
| Conductor - Pipe EMT Size       | <ul style="list-style-type: none"><li>• 1 1/4 in</li><li>• 1 1/2 in</li><li>• 2 in</li></ul>                                                                                             |
| Conductor - Copper Str Size     | <ul style="list-style-type: none"><li>• 10 AWG</li><li>• 9 AWG</li><li>• 8 AWG</li><li>• 7 AWG</li><li>• 6 AWG</li><li>• 5 AWG</li><li>• 4 AWG</li><li>• 3 AWG</li><li>• 2 AWG</li></ul> |
| Conductor - Copper Solid Size   | <ul style="list-style-type: none"><li>• 10 AWG</li><li>• 9 AWG</li><li>• 8 AWG</li><li>• 7 AWG</li><li>• 6 AWG</li><li>• 5 AWG</li><li>• 4 AWG</li><li>• 3 AWG</li></ul>                 |



|                                   |                |
|-----------------------------------|----------------|
| Conductor - Armored Cable Size    | • 2 AWG        |
| Conductor - Copper Solid Size     | N              |
| Conductor - Copper Str Size Range | 10 AWG-2 AWG   |
| Conductor - Copper Str Size Range | 10 AWG - 2 AWG |

### Dimensions

|                                 |           |
|---------------------------------|-----------|
| Dimension - Pad Width inch      | 1.00 in   |
| Package Height                  | 0.000 in  |
| Dimension - Height mm           | 60.5 mm   |
| Dimension - Height inch         | 2.38 in   |
| Package Weight                  | 0.000 lb. |
| Package Length                  | 0.000 in  |
| Package Width                   | 0.000 in  |
| Dimension - L Length Overall mm | 92 mm     |
| Dimension - Hole Size mm        | 8 mm      |
| Dimension - Hole Size inch      | 0.31 in   |
| Dimension - Width mm            | 19 mm     |
| Dimension - Width inch          | 0.75 in   |
| Dimension - Length Overall inch | 3.63 in   |

### General

|                     |                                                                                                                                                                 |
|---------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Product Family      | Grounding and Bonding<br>Connectors>Copper Mechanical<br>Grounding Connectors>Cable(s) to<br>Ground Rod/Pipe/Tube<br>(GAR/GD/GK)>LC Water Pipe<br>Ground Clamps |
| Material - Hardware | DURIUM™ Silicon Bronze                                                                                                                                          |
| Plated              | No                                                                                                                                                              |
| Sub Brand           | CLAMP                                                                                                                                                           |
| Product Type        | Mechanical                                                                                                                                                      |
| UPC                 | 781810142318                                                                                                                                                    |
| Type                | Ground Clamp                                                                                                                                                    |
| Material            | Bronze Alloy                                                                                                                                                    |
| Plating Type        | Unplated                                                                                                                                                        |
| UPC 12 Digit        | 781810142318                                                                                                                                                    |
| UPC 14 Digit GTIN   | 00781810142318                                                                                                                                                  |

### Logistics

|                       |      |
|-----------------------|------|
| Minimum Pack Quantity | 1    |
| Pallet Quantity       | 1800 |
| Carton Quantity       | 50   |



A Hubbell brand