



C6D, Cast Bronze Clamp, Armored Cable to Water Pipe

By Burndy
Catalog # [C6D](#)

Cast Bronze Clamp, Armored Cable to Water Pipe, 10 AWG - 2
AWG (Str.), 1/2" - 1" Water Pipe



Features

- Cast bronze clamp for armored cable to water pipe
- Zinc plated screws
- UL467 for direct burial in earth and concrete
- Supplied with silicon bronze hardware

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	NC
Certification - cULus	No
Certification - UL Listed Direct Burial	Yes
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	UL467
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor - Copper Solid Size	• 8 AWG • 7 AWG • 6 AWG • 5 AWG • 4 AWG • 3 AWG • 2 AWG
Conductor - Pipe EMT Size Range	1/2 in -1 in
Conductor - Pipe EMT Size	• 3/8 in • 1/2 in • 3/4 in • 1 in
Conductor - Armored Cable Size	Y
Conductor - Copper Solid Size Range	8 AWG-2 AWG
Conductor Type	• CU C Str-Size • CU C Solid-Size • Pipe EMT-Size
Conductor - Copper Str Size Range	10 AWG - 2 AWG

Conductor - Copper Str Size	• 10 AWG • 9 AWG • 8 AWG • 7 AWG • 6 AWG • 5 AWG • 4 AWG • 3 AWG • 2 AWG
-----------------------------	--

Dimensions

Dimension - Pad Width inch	0.63 in
Package Height	0.000 in
Dimension - Height mm	40.6 mm
Dimension - Height inch	1.60 in
Package Weight	0.000 lb.
Dimension - Width mm	27 mm
Dimension - Width inch	1.06 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	59 mm
Dimension - Length Overall inch	2.34 in

General

Plated	Y
Material - Hardware	DURIUM™ Silicon Bronze
UPC	781810142431
Material	Bronze Alloy
Plating Type	Zinc
UPC 12 Digit	781810142431
Hardware Type	Silicon Bronze
UPC 14 Digit GTIN	00781810142431

Logistics

Minimum Pack Quantity	1
Pallet Quantity	9800
Carton Quantity	25

Product Assets

[Catalog \[English\]](#)