




# C7, Cast Bronze Clamp, Cable to Water Pipe

By Burndy  
Catalog # [C7](#)

ARMWIRE 1-1/4 TO 2IN HUB



## Features

- Connects Armored Cable to Water Pipe

## Application

For Connecting Armored Cable To Water Pipe And Direct Burial In Earth And Concrete

## Specifications

|                                    |                      |
|------------------------------------|----------------------|
| Buy American Compliant             | Contact Manufacturer |
| Certification - cULus              | No                   |
| EU RoHS Indicator                  | Yes                  |
| Certification - UL Recognized      | No                   |
| Industry Standard(s)               | UL467                |
| Buy America(n) Qualified           | Contact Manufacturer |
| Certification - ETL                | No                   |
| Standards - Industry Standards Met | UL467                |
| Standards - RoHS Compliance        | CM                   |
| Status                             |                      |
| Certification - CSA Approved       | No                   |
| UL Listed                          | Yes                  |

## Conductor

|                                 |                                                                                                                                                                                          |
|---------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Conductor - Pipe EMT Size       | <ul style="list-style-type: none"><li>• 1 1/4 in</li><li>• 1 1/2 in</li><li>• 2 in</li></ul>                                                                                             |
| Conductor - Pipe EMT Size Range | 1 1/4 in-2 in                                                                                                                                                                            |
| Conductor - Copper Str Size     | <ul style="list-style-type: none"><li>• 10 AWG</li><li>• 9 AWG</li><li>• 8 AWG</li><li>• 7 AWG</li><li>• 6 AWG</li><li>• 5 AWG</li><li>• 4 AWG</li><li>• 3 AWG</li><li>• 2 AWG</li></ul> |
| Conductor - Copper Solid Size   | <ul style="list-style-type: none"><li>• 8 AWG</li><li>• 7 AWG</li><li>• 6 AWG</li><li>• 5 AWG</li><li>• 4 AWG</li></ul>                                                                  |

- 3 AWG
  - 2 AWG
- Conductor - Copper Solid Size Range 8 AWG-2 AWG
- Conductor - Armored Cable Size Y
- Conductor - Copper Str Size Range 10 AWG - 2 AWG
- Conductor Type
- CU C Str-Size
  - CU C Solid-Size
  - Pipe EMT-Size

## Dimensions

|                                 |         |
|---------------------------------|---------|
| Dimension - L Length Overall mm | 92 mm   |
| Dimension - Pad Width inch      | 1.00 in |
| Dimension - Height inch         | 2.38 in |
| Dimension - Height mm           | 60.5 mm |
| Dimension - Width inch          | 0.94 in |
| Dimension - Width mm            | 24 mm   |
| Dimension - Length Overall inch | 3.62 in |

## General

|                     |                   |
|---------------------|-------------------|
| Material - Hardware | Zinc Plated Steel |
| Sub Brand           | CLAMP             |
| Plated              | Y                 |
| Type                | Ground Clamp      |
| UPC 12 Digit        | 781810142424      |
| UPC 14 Digit GTIN   | 00781810142424    |
| Hardware Type       | Zinc Plated       |
| Material            | Bronze Alloy      |
| Plating Type        | Zinc              |
| UPC                 | 781810142424      |

## Logistics

|                       |      |
|-----------------------|------|
| Minimum Pack Quantity | 1    |
| Carton Quantity       | 20   |
| Pallet Quantity       | 3360 |

## Product Assets

[Catalog \[English\]](#)



A Hubbell brand