



C11B, Cast Bronze Ground Clamp, Cable to Water Pipe or Tube

By Burndy
Catalog # [C11B](#)

Cast Bronze Ground Clamp, Cable to Water Pipe or Copper Tube, 10 - 2 AWG, 1/2" - 1" Water Pipe

Features

- Connects grounding conductor to water pipe or copper tube
- B indicates Brass hardware

Application

For Bare Wire, Connecting Grounding Conductor To Water Pipe Or Copper Tube

Specifications

Certification - UL Recognized	No
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	UL467
Certification - ETL	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance	CM
Status	
Certification - UL Listed Direct	No
Burial	
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor - Pipe EMT Size Range	1/2 in-1 in
Conductor - Pipe EMT Size	• 1/2 in • 3/4 in • 1 in
Conductor - Copper Str Size	• 10 AWG • 9 AWG • 8 AWG • 7 AWG • 6 AWG • 5 AWG • 4 AWG • 3 AWG • 2 AWG
Conductor - Copper Solid Size	• 10 AWG • 9 AWG • 8 AWG • 7 AWG • 6 AWG • 5 AWG • 4 AWG • 3 AWG



Conductor - Armored Cable Size	• 2 AWG
Conductor - Copper Solid Size	N
Range	10 AWG-2 AWG
Conductor - Copper Str Size Range	10 AWG - 2 AWG

Dimensions

Dimension - Pad Width inch	0.63 in
Package Height	0.000 in
Dimension - Height mm	46 mm
Dimension - Height inch	1.81 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	57 mm
Dimension - Hole Size mm	8 mm
Dimension - Hole Size inch	0.31 in
Dimension - Width mm	16 mm
Dimension - Width inch	0.63 in
Dimension - Length Overall inch	2.25 in

General

Product Family	Grounding and Bonding Connectors>Copper Mechanical Grounding Connectors>Cable(s) to Ground Rod/Pipe/Tube (GAR/GD/GK)>LC Water Pipe Ground Clamps
Material - Hardware	Brass
Plated	Yes
Sub Brand	CLAMP
Product Type	Mechanical
UPC	781810142363
Type	Ground Clamp
Material	Bronze Alloy
Plating Type	Zinc Plated
UPC 12 Digit	781810142363
UPC 14 Digit GTIN	00781810142363

Logistics

Minimum Pack Quantity	1
Pallet Quantity	10000
Carton Quantity	100



A Hubbell brand