



C11K16D, Cast Bronze Ground Clamp for Water Pipe, Rebar, Ground Rod, to Tap Conductor

By Burndy
Catalog # C11K16D

Cast Bronze Ground Clamps, Water Pipe-1/2 " - 1 "(13 -25) (Run), Rebar-#4 -#6 (Run), Ground Rod -3/8"-1" (Run), Ground-#10-#2 Str. (Tap)

Features

- Lay-In Feature
- Connects Grounding Conductor to Water Pipe, Copper Tube, Ground Rod or Rebar
- Open face design allows for a fast lay-in on the tap conductor without need for cutting
- Reverse bottom clamp for smaller size, rebar or rod

Application

For Connecting Grounding Conductor To Water Pipe, Copper Tube, Ground Rod Or Rebar, Direct Burial Applications

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
Certification - cULus	No
EU RoHS Indicator	Yes
Certification - UL Listed Direct Burial	Yes
Industry Standard(s)	UL467
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Rebar Size	• 4 • 5 • 6
Conductor - Rebar Size Range	4 -6
Conductor - Pipe EMT Size Range	1/2 in-1 in
Conductor - Pipe EMT Size	• 1/2 in • 3/4 in • 1 in
Conductor - Rod Size Range	3/8 in-1 in
Conductor - Copper Str Size Range	10 AWG-2 AWG
Conductor - Copper Str Size	• 10 AWG • 9 AWG • 8 AWG

Conductor - Rod Size	• 7 AWG
	• 6 AWG
	• 5 AWG
	• 4 AWG
	• 3 AWG
	• 2 AWG
	• 3/8 in
	• 1/2 in
	• 5/8 in
	• 3/4 in
	• 7/8 in
	• 1 in

Dimensions

Package Height	0.000 in
Dimension - Height mm	41.7 mm
Length	1.39 in
Dimension - Height inch	1.64 in
Package Weight	0.000 lb.
Dimension - Width mm	17 mm
Dimension - Width inch	0.66 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	58 mm
Height	0.66 in
Width	2.28 in
Dimension - Length Overall inch	2.28 in
Dimensions	1.39 in x 2.28 in x 0.66 in

General

Plated	N
Material - Hardware	DURIUM™ Silicon Bronze
Sub Brand	CLAMP
UPC	781810358641
Type	Ground Clamp
Material	Copper
Plating Type	Unplated
UPC 12 Digit	781810358641
UPC 14 Digit GTIN	00781810358641

Logistics

Pallet Quantity	8000
-----------------	------

Carton Quantity

100

Product Assets

[Catalog \[English\]](#)



A Hubbell brand

© 2026 Hubbell Incorporated. All rights reserved
BRDY_MX-C11K16D-SPEC-EN | REV 5/2026