



## **C11N, Cast Bronze Ground Clamp, Cable to Water Pipe or Tube**

By Burndy

Catalog # [C11N](#)

Cast Bronze Ground Clamp, Cable to Water Pipe or Copper Tube, 10 - 2 AWG, 1/2" - 1" Water Pipe, pipe clamp:50 in-lb



Features

- Connects grounding conductor to water pipe or copper tube

Application

For Bare Wire, Connecting Grounding Conductor To Water Pipe Or Copper Tube

Specifications

|                                         |                      |
|-----------------------------------------|----------------------|
| Certification - UL Recognized           | No                   |
| Buy American Compliant                  | Contact Manufacturer |
| Certification - cULus                   | No                   |
| Buy America(n) Qualified                | Contact Manufacturer |
| Industry Standard(s)                    | UL467                |
| Certification - ETL                     | No                   |
| Standards - Industry Standards Met      | UL467                |
| Standards - RoHS Compliance             | NC                   |
| Status                                  |                      |
| Certification - UL Listed Direct Burial | No                   |
| UL Listed                               | Yes                  |
| Certification - CSA Approved            | No                   |

Conductor

|                                 |                                                                                                                                                                                          |
|---------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Conductor - Pipe EMT Size Range | 1/2 in-1 in                                                                                                                                                                              |
| Conductor - Pipe EMT Size       | <ul style="list-style-type: none"><li>• 1/2 in</li><li>• 3/4 in</li><li>• 1 in</li></ul>                                                                                                 |
| Conductor - Copper Str Size     | <ul style="list-style-type: none"><li>• 10 AWG</li><li>• 9 AWG</li><li>• 8 AWG</li><li>• 7 AWG</li><li>• 6 AWG</li><li>• 5 AWG</li><li>• 4 AWG</li><li>• 3 AWG</li><li>• 2 AWG</li></ul> |
| Conductor - Copper Solid Size   | <ul style="list-style-type: none"><li>• 10 AWG</li><li>• 9 AWG</li><li>• 8 AWG</li><li>• 7 AWG</li><li>• 6 AWG</li><li>• 5 AWG</li><li>• 4 AWG</li><li>• 3 AWG</li><li>• 2 AWG</li></ul> |

|                                     |                |
|-------------------------------------|----------------|
| Conductor - Armored Cable Size      | N              |
| Conductor - Copper Solid Size Range | 10 AWG-2 AWG   |
| Conductor - Copper Str Size Range   | 10 AWG - 2 AWG |

Dimensions

|                                 |           |
|---------------------------------|-----------|
| Dimension - Pad Width inch      | 0.63 in   |
| Package Height                  | 0.000 in  |
| Dimension - Height mm           | 46 mm     |
| Dimension - Height inch         | 1.81 in   |
| Package Weight                  | 0.000 lb. |
| Package Length                  | 0.000 in  |
| Package Width                   | 0.000 in  |
| Dimension - L Length Overall mm | 57 mm     |
| Dimension - Hole Size mm        | 8 mm      |
| Dimension - Hole Size inch      | 0.31 in   |
| Dimension - Width mm            | 16 mm     |
| Dimension - Width inch          | 0.63 in   |
| Dimension - Length Overall inch | 2.25 in   |

General

|                            |                                                                                                                                                                                      |
|----------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Product Family             | Grounding and Bonding<br>Connectors>Copper Mechanical<br>Grounding Connectors>Cable(s) to<br>Ground Rod/Pipe/Tube<br>(GAR/GD/GK)>LC Water Pipe<br>Ground Clamps<br>Zinc Plated Steel |
| Material - Hardware Plated | No                                                                                                                                                                                   |
| Sub Brand                  | CLAMP                                                                                                                                                                                |
| Product Type               | Mechanical                                                                                                                                                                           |
| UPC                        | 781810142288                                                                                                                                                                         |
| Type                       | Ground Clamp                                                                                                                                                                         |
| Material                   | Bronze Alloy                                                                                                                                                                         |
| Plating Type               | Unplated                                                                                                                                                                             |
| UPC 12 Digit               | 781810142288                                                                                                                                                                         |
| UPC 14 Digit GTIN          | 00781810142288                                                                                                                                                                       |

Logistics

|                       |       |
|-----------------------|-------|
| Minimum Pack Quantity | 1     |
| Pallet Quantity       | 10000 |
| Carton Quantity       | 100   |

Product Assets

[Catalog \[English\]](#)



A Hubbell brand