



C6, Cast Bronze Clamp, Armored Cable to Water Pipe

By Burndy
Catalog # [C6](#)

Cast Bronze Clamp, Armored Cable to Water Pipe, 10 AWG - 2 AWG (Str.), 1/2" -1" Water Pipe,pipe clamp:50 in-lb

Features

- Connects Armored Cable to Water Pipe

Application

For Connecting Armored Cable To Water Pipe

Specifications

Buy American Compliant	Contact Manufacturer
Certification - cULus	N
EU RoHS Indicator	Yes
Certification - UL Recognized	N
Industry Standard(s)	UL467
Buy America(n) Qualified	Contact Manufacturer
Certification - ETL	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
Certification - CSA Approved	Yes
UL Listed	Yes

Conductor

Conductor - Pipe EMT Size	• 3/8 in • 1/2 in • 3/4 in • 1 in
Conductor - Pipe EMT Size Range	3/8 in-1 in
Conductor - Copper Str Size	• 10 AWG • 9 AWG • 8 AWG • 7 AWG • 6 AWG • 5 AWG • 4 AWG • 3 AWG • 2 AWG
Conductor - Copper Solid Size	• 8 AWG • 7 AWG • 6 AWG • 5 AWG • 4 AWG • 3 AWG



Conductor - Copper Solid Size Range	• 2 AWG 8 AWG-2 AWG
Conductor - Armored Cable Size	Y
Conductor - Copper Str Size Range	10 AWG - 2 AWG
Conductor Type	• CU C Str-Size • CU C Solid-Size • Pipe EMT-Size

Dimensions

Dimension - L Length Overall mm	59 mm
Dimension - Pad Width inch	0.63 in
Dimension - Height inch	1.60 in
Dimension - Height mm	40.6 mm
Dimension - Thread Size	-
Dimension - Width inch	1.06 in
Dimension - Width mm	27 mm
Dimension - Length Overall inch	2.34 in

General

Material - Hardware	Zinc Plated Steel
Trade Name	N
Sub Brand	CLAMP
Plated	Y
Type	Ground Clamp
UPC 12 Digit	781810142394
UPC 14 Digit GTIN	00781810142394
Hardware Type	Zinc Plated
Material	Bronze Alloy
Plating Type	Zinc
UPC	781810142394

Logistics

Minimum Pack Quantity	1
Carton Quantity	25
Pallet Quantity	7425

Product Assets

[Catalog \[English\]](#)



A Hubbell brand