



CL501, Copper Lay-in Lug, #14-4 AWG, #10 Stud, Tin Plate

By Burndy
Catalog # [CL501TN](#)

Copper Lay-in Lug, Accommodates #14-4 AWG Copper, #10 Stud, Tin Plated, UL467 Listed for Direct Burial



Features

- UL2703 for Solar Applications
- UL467 for Direct Burial

Application

For Direct Burial Applications In Concrete Or Earth, For Fast Lay-In Of The Conductor Without The Need For Cutting Or Breaking, For Solar Panel Grounding

Specifications

Certification - UL Recognized	N
Buy American Compliant	No
Certification - cULus	N
Industry Standard(s)	UL467
Certification - ETL	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance	CM
Status	
Certification - UL Listed Direct Burial	Y
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Copper Str Size	• 14 AWG
	• 12 AWG
	• 10 AWG
	• 9 AWG
	• 8 AWG
	• 7 AWG
	• 6 AWG
	• 5 AWG
	• 4 AWG
Conductor - Copper Solid Size	• 14 AWG
	• 13 AWG
	• 12 AWG
	• 11 AWG
	• 10 AWG
	• 9 AWG
	• 8 AWG
	• 7 AWG
	• 6 AWG
	• 5 AWG
	• 4 AWG

Conductor - Copper Solid Size Range	14 AWG-4 AWG
Conductor Type	CU C Str-Size
Conductor - Copper Str Size Range	14 AWG - 4 AWG

Dimensions

Package Height	0.000 in
Dimension - Height mm	21.6 mm
Dimension - Height inch	0.85 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	29 mm
Dimension - Thread Size	-
Dimension - Hole Size mm	6 mm
Dimension - Hole Size inch	0.22 in
Dimension - Stud Size inch	17/64
Dimension - Width mm	10 mm
Dimension - Width inch	0.38 in
Dimension - D inch	0.47 in
Dimension - N inch	0.19 in
Dimension - Length Overall inch	1.13 in

General

Product Family	Grounding and Bonding Connectors>Copper Mechanical Grounding Connectors>Lay In Ground Clamps
Trade Name	QIKLUG
Material - Hardware Plated	Stainless Steel Yes
Sub Brand	QIKLUG
Product Type	Mechanical
UPC	781810352342
Type	Open-Faced
Material	Copper
Plating Type	Tin
UPC 12 Digit	781810352342
UPC 14 Digit GTIN	00781810352342

Logistics

Minimum Pack Quantity	100
Pallet Quantity	2700
Carton Quantity	700

Product Assets

[Catalog \[English\]](#)

[Installation Manual \[English\]](#)



A Hubbell brand