



ES25R25RBOX, Insulated Aluminum  
Service Entrance Compression Sleeve

By Burndy  
Catalog # [ES25R25RBOX](#)

Insulated Service Entrance Sleeve

Features

- Pre-insulated service entrance compression connector
- Polyethylene caps prevent dirt from accumulating in barrel, grip cable for easy two-hand installation, seal out moisture
- Connector is anchored to jacket assuring the connector is under the die when crimping
- Prefilled with joint compound and stripealed to limit oxidation and increase life of the connection

Specifications

|                               |    |
|-------------------------------|----|
| Certification - ETL           | No |
| Certification - UL Recognized | No |
| Standards - RoHS Compliance   | CM |
| Status                        |    |
| Certification - cULus         | No |
| UL Listed                     | No |
| Certification - CSA Approved  | No |

Conductor

|                               |                |
|-------------------------------|----------------|
| Conductor - Copper Str Size A | 1/0 STR        |
| Conductor - Copper Str Size B | 1/0 STR        |
| Conductor - AL Str Size A     | 1/0 STR        |
| Conductor - AL Str Size B     | 1/0 STR        |
| Conductor - ACSR Str Size A   | 1/0 STR, 1 STR |
| Conductor - ACSR Str Size B   | 1/0 STR, 1 STR |

Dimensions

|                |           |
|----------------|-----------|
| Package Height | 0.000 in  |
| Package Weight | 0.000 lb. |
| Package Length | 0.000 in  |

|                              |          |
|------------------------------|----------|
| Package Width                | 0.000 in |
| Dimension - L Length Overall | 70 mm    |
| Dimension - Outside Diameter | .75 in   |
| Dimension - Length Overall   | 2.75 in  |

General

|                           |                                       |
|---------------------------|---------------------------------------|
| Plated                    | Y                                     |
| Insulation Type           | Nylon                                 |
| Trade Name                | INSULINK™                             |
| Die Index                 | BG                                    |
| UPC                       | 781810191705                          |
| Type                      | Insulated Service Entrance Connectors |
| Prefilled Oxide Inhibitor | Y                                     |
| Insulation                | Y                                     |
| Material                  | Aluminum                              |
| Plating Type              | Unplated                              |
| UPC 12 Digit              | 781810191705                          |
| UPC 14 Digit GTIN         | 00781810191705                        |

Logistics

|                       |       |
|-----------------------|-------|
| Minimum Pack Quantity | 1     |
| Pallet Quantity       | 11136 |
| Carton Quantity       | 24    |

Product Assets

[Catalog \[English\]](#)