

ES25R4W, Insulated Aluminum Service Entrance Compression Sleeve

By Burndy
Catalog # [ES25R4W](#)



Insulated AL service entrance compression sleeve

Features

- Pre-insulated service entrance compression connector
- Polyethylene caps prevent dirt from accumulating in barrel, grip cable for easy two-hand installation, seal out moisture
- Connector is anchored to jacket assuring the connector is under the die when crimping
- Prefilled with joint compound and stripealed to limit oxidation and increase life of the connection

Specifications

Certification - UL Recognized	No
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
EU RoHS Indicator	Yes
Buy America(n) Qualified	Contact Manufacturer
Certification - ETL	No
Standards - RoHS Compliance Status	CM
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Size A	• 1/0 AWG • 1 AWG (19 Str.)
Conductor - AL Str Size B	• 6 AWG • 5 AWG
Conductor - AL Str Size A Range	1/0 AWG-1 AWG (19 Str.)
Conductor - AL Str Size B Range	6 AWG-5 AWG
Conductor - ACSR Str Size A	• 1 (6/1) Robin AWG • 1/0 (6/1) Raven AWG
Conductor - ACSR Str Size B	6 (6/1) Turkey AWG
Conductor - ACSR Str Size A Range	1 (6/1) Robin AWG-1/0 (6/1) Raven AWG
Conductor - ACSR Str Size B Range	6 (6/1) Turkey AWG
Conductor - Copper Str Size A	• 1/0 AWG • 1 AWG (19 Str.)
Conductor - Copper Str Size B	• 6 AWG • 5 AWG
Conductor - Copper Str Size A Range	1/0 AWG-1 AWG (19 Str.)

Conductor - Copper Solid Size B	4 AWG
Conductor - Copper Str Size B Range	6 AWG-5 AWG

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	70 mm
Dimension - Outside Diameter inch	.75 in
Dimension - Length Overall inch	2.75 in

General

Insulation Type	Nylon
Trade Name	INSULINK™
Die Index	BG or 5/8
Prefilled Oxide Inhibitor	Y
Insulation	Y
Plated	Y
Sub Brand	INSULINK
UPC	781810149201
Color Code - Side B	Blue
Color Code - Side A	Yellow
Type	ES
Construction Material - Main Material	Aluminum
Plating Type	Tin - Hot Dipped
UPC 12 Digit	781810149201
UPC 14 Digit GTIN	00781810149201

Logistics

Minimum Pack Quantity	100
Pallet Quantity	24000
Carton Quantity	100

Product Assets

[Catalog \[English\]](#)