




GAR3905BU, Mech Ground Conn, Conductor to Water Pipe

By Burndy
Catalog # [GAR3905BU](#)

Mechanical Grounding Connector, Conductor to Water Pipe, 4-4/O AWG, 4"-5" Pipe, 3/8" Stud



Features

- Cable clamp swivels at 90°
- One-wrench installation for simplified installation
- Rated for Direct Burial in earth or concrete
- UL467 Listed for the US and Canadian Markets
- High conductivity copper ground connector for connecting a small/medium range copper ground conductor to water pipe, structural and reinforcing rod shapes

Application

For Connecting A Small To Medium Range Copper Ground Conductor To Water Pipe As Well As Structural And Reinforcing Rod Shapes

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
Certification - cULus	No
EU RoHS Indicator	Yes
Certification - UL Listed Direct Burial	Yes
Industry Standard(s)	UL467
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor - Pipe or Round Tube Size	4 - 5 in
Conductor - Copper Solid Size Range	4 AWG - 4/O AWG
Conductor - Copper Str Size Range	4-4/O
Conductor - Copper Str Size	• 4 • 3 • 2 • 1 • 1/O • 2/O • 3/O

Conductor - Copper Tube Std Size Range	• 4/O 4-5
Conductor - Copper Tube Std Size	• 4 • 5

Dimensions

Package Height	0.000 in
Dimension - Height mm	190.5 mm
Dimension - Height inch	7.50 in
Package Weight	0.000 lb.
Dimension - Width mm	191 mm
Dimension - Width inch	7.50 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - B Length inch	1.75 in
Dimension - Outside Diameter inch	5.56 in
Dimension - Length Overall inch	1.75 in

Force Related

Installation Torque	200 LBS/in
Recommended in-lb	

General

Plated	N
Material - Hardware	DURIUM™ Silicon Bronze
Sub Brand	MECHANICAL CONNECTOR
UPC	781810001523
Type	GAR-BU
U Bolt Type	422
Material	Copper Alloy
Plating Type	Unplated
UPC 12 Digit	781810001523
UPC 14 Digit GTIN	00781810001523

Logistics

Pallet Quantity	1170
Carton Quantity	15

Product Assets

[Catalog \[English\]](#)



A Hubbell brand