

# FD70D16SV, Substation - Copper Stud Connector

By Burndy  
Catalog # [FD70D16SV](#)

Copper Stud Connectors



### Features

- For use on stud to pads
- Allows for bolting cable and tubing terminals to equipment studs
- Hex captured bolts provide one-wrench installation

### Application

Substation

### Specifications

|                                    |    |
|------------------------------------|----|
| Certification - ETL                | No |
| Certification - UL Recognized      | No |
| Standards - RoHS Compliance Status | EX |
| Certification - cULus              | No |
| UL Listed                          | No |
| Certification - CSA Approved       | No |

### Conductor

|                                    |             |
|------------------------------------|-------------|
| Conductor - Connection Combination | Stud to Pad |
|------------------------------------|-------------|

### Configuration

|                                        |                |
|----------------------------------------|----------------|
| Physical Attribute - Pad Orientation   | In-line        |
| Physical Attribute - Pad Configuration | 4x4 - 4 holes  |
| Physical Attribute - Number of Holes   | 4              |
| Connector Type                         | Stud Connector |

### Dimensions

|                                   |          |
|-----------------------------------|----------|
| Dimension - Pin Diameter inch     | 3.000 in |
| Dimension - Pin Diameter fraction | 3 in     |

|                                           |           |
|-------------------------------------------|-----------|
| Dimension - Pad Width inch                | 4.00 in   |
| Package Height                            | 0.000 in  |
| Dimension - Height mm                     | 0 mm      |
| Dimension - Bolt Size fraction            | 5/8       |
| Package Weight                            | 0.000 lb. |
| Package Length                            | 0.000 in  |
| Dimension - F Width Center to Center inch | 1.75 in   |
| Package Width                             | 0.000 in  |
| Dimension - L Length Overall mm           | 209 mm    |
| Dimension - B Length inch                 | 2.88 in   |
| Dimension - D inch                        | 4.00 in   |
| Dimension - N inch                        | 1.13 in   |
| Dimension - Thread Size                   | 5/8-12    |
| Dimension - Threads per inch              | 12        |
| Dimension - Length Overall inch           | 8.24 in   |

### General

|                     |                        |
|---------------------|------------------------|
| Plated              | Y                      |
| Material - Hardware | DURIUM™ Silicon Bronze |
| UPC                 | 781810118771           |
| Type                | Studs                  |
| Material            | Copper Alloy           |
| Plating Type        | Silver                 |
| UPC 12 Digit        | 781810118771           |
| UPC 14 Digit GTIN   | 00781810118771         |

### Logistics

|                       |   |
|-----------------------|---|
| Minimum Pack Quantity | 1 |
| Pallet Quantity       | 1 |
| Carton Quantity       | 1 |

### Product Assets

[Catalog \[English\]](#)