



GCM4C, Mechanical Grounding Connector, 2 Cables to Bar

By Burndy

Catalog # [GCM4C](#)

Mechanical Grounding Connector, 2 Copper Cables to 1/4" Thick
Bar, 8 AWG (Sol.) - 4 AWG (Str.), 3/8" Stud



Features


- High copper alloy ground connector for joining a wide range of 2 parallel cables to 1/2" thick bar
- Type GC separates cable from bar
- Type GCM clamps cable direct to bar surface
- One wrench installation
- UL467 Listed
- Suitable for Direct Burial in earth or concrete

Specifications

Certification - UL Recognized	No
Buy American Compliant	Yes
Certification - cULus	No
Buy America(n) Qualified	• Buy American Act Compliant (All status valid till December 2026) • BABA Compliant (All status valid till December 2026)
Industry Standard(s)	UL467
Certification - ETL	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
Certification - UL Listed Direct Burial	Yes
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size	• 8 AWG • 7 AWG • 6 AWG • 5 AWG • 4 AWG
Conductor - Copper Solid Size	• 8 AWG • 7 AWG • 6 AWG • 5 AWG • 4 AWG
Conductor - Copper Solid Size Range	8 AWG-4 AWG
Conductor - Copper Str Size Range	8 AWG - 4 AWG



Dimensions

Package Height	0.000 in
Dimension - Height mm	34.5 mm
Dimension - Height inch	1.36 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	22 mm
Dimension - Width fraction	1 in
Dimension - Bar Width inch	1.04 in
Dimension - Bar Thickness mm	6 mm
Dimension - Bar Width mm	26 mm
Dimension - Bar Thickness inch	0.25 in
Dimension - Width mm	26 mm
Dimension - Width inch	1.04 in
Dimension - Bar Length mm	22 mm
Dimension - Bar Length inch	0.88 in
Dimension - Length Overall inch	0.88 in

Force Related

Installation Torque	240 LBS/in
Recommended in-lb	

General

Material Type - Screw	DURIUM™ Silicon Bronze
Physical Attribute - Screw Type	Hexagonal Bolt
Plated	N
UPC	781810001769
Material	Copper Alloy, Cast
Plating Type	Unplated
UPC 12 Digit	781810001769
UPC 14 Digit GTIN	00781810001769

Logistics

Minimum Pack Quantity	20
Pallet Quantity	1
Carton Quantity	25

Product Assets

[Catalog \[English\]](#)