



GAR2029W, Mech Ground Conn, Cable to Rod or Pipe, Tin Plated

By Burndy
Catalog # [GAR2029W](#)



Mechanical Grounding Connector, Cable to Rod or Pipe, 2/0 AWG (Sol) -250 kcmil, 3" Pipe, 3"-3-1/2" Rod, Tin Plated.

Features

- Parallel or 90° Copper Cable Connection
- One-wrench installation
- Rated for Direct Burial in earth or concrete

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
Certification - cULus	No
Certification - UL Listed Direct Burial	Yes
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	UL467
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Pipe or Round Tube Size	3 in
Conductor - Copper Solid Size	• 2/0 • 3/0 • 4/0
Conductor - Copper Solid Size Range	2/0 AWG-250 Kcmil
Conductor - Rod Size Range	3
Conductor Type	• CU C Solid-Size • CU C Str-Size • CU Tube Std-Size • Rod-Size
Conductor - Copper Str Size Range	1/0 AWG - 250 kcmil
Conductor - Copper Str Size	• 1/0 • 2/0 • 3/0 • 4/0 • 250
Conductor - Rod Size	3 - 3.5 in
Conductor - Copper Tube Std Size Range	3-3 1/2

Conductor - Copper Tube Std Size	• 3 • 3 1/2
----------------------------------	---

Dimensions

Package Height	0.000 in
Dimension - Height mm	143 mm
Dimension - Height inch	5.63 in
Package Weight	0.000 lb.
Dimension - Width mm	122 mm
Dimension - Width inch	4.81 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	46 mm
Dimension - B Length inch	3.50 in
Dimension - Outside Diameter inch	3.50 in
Dimension - Length Overall inch	1.81 in

Force Related

Installation Torque Recommended in-lb	240 LBS/in
---------------------------------------	------------

General

Plated	Y
Material - Hardware UPC	DURIUM™ Silicon Bronze 781810176320
U Bolt Type	267
Material	Copper Alloy
Plating Type	Tin - Hot Dipped
UPC 12 Digit	781810176320
UPC 14 Digit GTIN	00781810176320

Logistics

Minimum Pack Quantity	8
Pallet Quantity	720
Carton Quantity	3

Product Assets

[Catalog \[English\]](#)



A Hubbell brand