



GAR204C, Mech Grounding Connector, Cable to Rod or Pipe

By Burndy
Catalog # [GAR204C](#)



Mechanical Grounding Connector, Cable to Rod or Pipe, 8 AWG (Sol.) - 4 AWG (Str.), 3" to 3-1/2" Rod, 3" Pipe, Bright Dipped

Features

- Parallel or 90° Copper Cable Connection
- One-wrench installation
- Rated for Direct Burial in earth or concrete

Application

For Joining A Range Of Cable, Parallel Or At Right Angles To Rod Or Tube, Direct Burial Cable, Fence Post

Specifications

Certification - UL Recognized	No
Certification - cULus	No
EU RoHS Indicator	Yes
Industry Standard(s)	UL467
Certification - ETL	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
Certification - UL Listed Direct Burial	Yes
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor - Pipe or Round Tube Size	3 in
Conductor - Rod Size Range	3 in-3 1/2 in
Conductor - Copper Str Size	• 9 AWG • 8 AWG • 7 AWG • 6 AWG • 5 AWG • 4 AWG
Conductor - Rod Size	3 - 3.5 in
Conductor - Copper Solid Size	• 8 AWG • 7 AWG • 6 AWG • 5 AWG • 4 AWG • 3 AWG
Conductor - Copper Solid Size Range	8 AWG-4 AWG
Conductor Type	• CU C Solid-Size • CU C Str-Size

- CU Tube Std-Size
- Rod-Size

Conductor - Copper Str Size Range	9 AWG - 4 AWG
Conductor - Copper Tube Std Size Range	3 IPS IPS
Conductor - Copper Tube Std Size	3 IPS IPS

Dimensions

Package Height	0.000 in
Dimension - Height mm	143 mm
Dimension - Height inch	5.63 in
Dimension - Height fraction	5-5/8 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	33 mm
Dimension - Outside Diameter inch	3.50 in
Dimension - Width fraction	4-3/4 in
Dimension - Width mm	122 mm
Dimension - Width inch	4.81 in
Dimension - B Length inch	3.50 in
Dimension - Length Overall inch	1.31 in

Force Related

Installation Torque Recommended in-lb	240 LBS/in
---------------------------------------	------------

General

Material - Hardware Plated	DURIUM™ Silicon Bronze N
Sub Brand	MECHANICAL CONNECTOR
UPC	781810236208
Type	GAR
U Bolt Type	267
Material	Copper Alloy
Plating Type	Bright Dipped
UPC 12 Digit	781810236208
UPC 14 Digit GTIN	00781810236208

Logistics

Pallet Quantity 1040
Carton Quantity 20

Product Assets

[Catalog \[English\]](#)



A Hubbell brand