



GAR2426, Mech Ground Conn, Cable to Rod or Pipe

By Burndy
Catalog # [GAR2426](#)

Mechanical Grounding Connector, Cable to Rod or Pipe, 4 AWG (Sol.) - 2/0 AWG (Str.), 5" Pipe

Features

- Parallel or 90° Copper Cable Connection
- One-wrench installation
- Rated for Direct Burial in earth or concrete

Application

For Joining A Range Of Cable, Parallel Or At Right Angles To Rod Or Tube, Direct Burial Cable, Fence Post

Specifications

Certification - UL Recognized	No
Buy American Compliant	No
Certification - cULus	No
Industry Standard(s)	UL467
Certification - ETL	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance	EX
Status	
Certification - UL Listed Direct Burial	Yes
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor - Pipe or Round Tube Size	5 in
Conductor - Copper Str Size	• 5 AWG • 4 AWG • 3 AWG • 2 AWG • 1 AWG • 1/0 • 2/0 AWG
Conductor - Copper Solid Size	• 4 AWG • 3 AWG • 2 AWG • 1 AWG • 1/0 AWG • 2/0 AWG • 3/0 AWG
Conductor - Copper Solid Size Range	4 AWG-2/0 AWG
Conductor Type	• CU C Solid-Size • CU C Str-Size • CU Tube Std-Size



	• Rod-Size
Conductor - Copper Str Size Range	5 AWG - 2/0 AWG
Conductor - Copper Tube Std Size Range	5 IPS IPS
Conductor - Copper Tube Std Size	5 IPS IPS

Dimensions

Package Height	0.000 in
Dimension - Height mm	196.9 mm
Dimension - Height inch	7.75 in
Dimension - Height fraction	7-3/4 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	40 mm
Dimension - Outside Diameter inch	5.56 in
Dimension - Width fraction	6-7/8 in
Dimension - Width mm	175 mm
Dimension - Width inch	6.88 in
Dimension - B Length inch	4.50 in
Dimension - Length Overall inch	1.56 in

Force Related

Installation Torque Recommended in-lb	240 LBS/in
---------------------------------------	------------

General

Product Family	Grounding and Bonding Connectors>Copper Mechanical Grounding Connectors>Cable(s) to Ground Rod/Pipe/Tube (GAR/GD/GK)>Single Conductor(GAR)
Material - Hardware Plated	DURIUM™ Silicon Bronze No
Sub Brand	MECHANICAL CONNECTOR
Product Type	Mechanical
UPC	781810237854
Type	GAR
U Bolt Type	422
Material	Copper Alloy
Plating Type	Bright Dipped
UPC 12 Digit	781810237854
UPC 14 Digit GTIN	00781810237854

Logistics

Minimum Pack Quantity1

Product Assets

Catalog [English]



A Hubbell brand

© 2026 Hubbell Incorporated. All rights reserved
BRDY-GAR2426-SPEC-EN | REV 7/2026