



GAR3903BU, Mech Ground Conn, Conductor to Water Pipe

By Burndy
Catalog # [GAR3903BU](#)

Mechanical Grounding Connector, Conductor to Water Pipe, 4-4/O AWG, 1-1/4"-2" Pipe, 3/8" Stud

Features

- Cable clamp swivels at 90°
- One-wrench installation for simplified installation
- Rated for Direct Burial in earth or concrete
- UL467 Listed for the US and Canadian Markets
- High conductivity copper ground connector for connecting a small/medium range copper ground conductor to water pipe, structural and reinforcing rod shapes

Application


For Connecting A Small To Medium Range Copper Ground Conductor To Water Pipe As Well As Structural And Reinforcing Rod Shapes

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
Certification - cULus	No
EU RoHS Indicator	Yes
Certification - UL Listed Direct Burial	Yes
Industry Standard(s)	UL467
Certification - CSA Approved	No

Conductor

Conductor - Pipe or Round Tube Size	1.25 - 2 in
Conductor - Copper Solid Size Range	4 AWG - 4/O AWG
Conductor - Copper Str Size Range	4-4/O
Conductor - Copper Str Size	• 4 • 3 • 2 • 1 • 1/O • 2/O • 3/O • 4/O



Conductor - Copper Tube Std Size Range	1 1/4-2
Conductor - Copper Tube Std Size	• 1 1/4 • 2

Dimensions

Package Height	0.000 in
Dimension - Height mm	101.6 mm
Dimension - Height inch	4.00 in
Package Weight	0.000 lb.
Dimension - Width mm	108 mm
Dimension - Width inch	4.25 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - B Length inch	1.75 in
Dimension - Outside Diameter inch	2.38 in
Dimension - Length Overall inch	1.75 in

Force Related

Installation Torque Recommended in-lb	200 LBS/in
---------------------------------------	------------

General

Plated	N
Material - Hardware	DURIUM™ Silicon Bronze
Sub Brand	MECHANICAL CONNECTOR
UPC	781810001509
Type	GAR-BU
U Bolt Type	1032
Material	Copper Alloy
Plating Type	Unplated
UPC 12 Digit	781810001509
UPC 14 Digit GTIN	00781810001509

Logistics

Pallet Quantity	2000
Carton Quantity	20

Product Assets

[Catalog \[English\]](#)



A Hubbell brand