




GL2929, Mechanical Ground Connector, 2 Copper Cables to Bar

By Burndy
Catalog # [GL2929](#)



Mechanical Ground Connector; 2 Copper Cables to 1/4" Bar, 2/0 AWG
Sol - 250 kcmil Copper, 1/2" Stud

Features

- Rated for Direct Burial in earth or concrete
- UL467 Listed
- One wrench installation

Application

For Joining A Wide Range Of Two Parallel Copper Cables To 1/4 IN Thick Bar, Direct Burial In Concrete Or Ground

Specifications

Certification - UL Recognized	No
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	UL467
Certification - ETL	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance	EX
Status	
Certification - UL Listed Direct Burial	Yes
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size	• 2/0 AWG • 3/0 AWG • 4/0 AWG • 250 kcmil
Conductor - Copper Solid Size	• 2/0 AWG • 3/0 AWG • 4/0 AWG
Conductor - Copper Solid Size Range	2/0 AWG-4/0 AWG
Conductor - Copper Str Size Range	2/0 AWG-250 kcmil

Dimensions

Dimension - Pad Width inch	1.22 in
Package Height	0.000 in
Dimension - Height mm	57.2 mm
Dimension - Height inch	2.25 in

Dimension - Height fraction	2-1/4 in
Package Weight	0.000 lb.
Package Length	0.000 in
Dimension - F Width Center to Center inch	1.25 in
Package Width	0.000 in
Dimension - Width fraction	2-1/4 in
Dimension - Width mm	57 mm
Dimension - Width inch	2.25 in
Dimension - B Length inch	2.22 in
Dimension - Length Side B inch	2.44 in
Dimension - D inch	2.25 in

Force Related

Installation Torque Recommended in-lb	480 LBS/in
---------------------------------------	------------

General

Product Family	Grounding and Bonding Connectors>Copper Mechanical Grounding Connectors>Cable(s) to Bar/Flat
Material Type - Screw	DURIUM™ Silicon Bronze
Physical Attribute - Screw Type	Hexagonal Bolt
Plated	No
Sub Brand	MECHANICAL CONNECTOR
Product Type	Mechanical
UPC	781810260029
Type	GL
Material	Copper Alloy
Plating Type	Unplated
UPC 12 Digit	781810260029
UPC 14 Digit GTIN	00781810260029

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1
Carton Quantity	6

Product Assets

[Catalog \[English\]](#)