



GP6434, Mech Grounding Conn, 2 Cables to Rod or Pipe

By Burndy
Catalog # [GP6434](#)

2 Cables to Rod or Pipe, 300-500 kcmil, 3/8" Pipe, 5/8" to 3/4" Rod, 3/8 Stud

Features

- Rated for Direct Burial in earth or concrete
- UL467 Listed for the US and Canadian Markets
- One-wrench installation

Application

For Joining A Range Of Parallel Copper Cables Perpendicular To Rod, Pipe Or Column, Direct Burial In Earth Or Concrete

Specifications

Certification - UL Recognized	No
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	UL467
Certification - ETL	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance	EX
Status	
Certification - UL Listed Direct Burial	Yes
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor - Rod Size Range	5/8 in-3/4 in
Conductor - Copper Str Size	• 300 • 350 • 400 • 450 • 500
Conductor - Rod Size	• 5/8 in • 3/4 in
Conductor - Copper Solid Size	18 AWG
Conductor - Copper Solid Size Range	18 AWG
Conductor - Copper Str Size Range	300-500
Conductor - Copper Str Size B Range	0.375
Conductor - Copper Tube Std Size Range	5/8-3/4
Conductor - Copper Tube Std Size	5/8



- 3/4

Dimensions

Package Height	0.000 in
Dimension - Height mm	88.9 mm
Dimension - Height inch	3.50 in
Dimension - Height fraction	3-1/2 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	65 mm
Dimension - Width fraction	2-5/9 in
Dimension - Width mm	65 mm
Dimension - Width inch	2.56 in
Dimension - B Length inch	2.00 in
Dimension - Length Overall inch	2.56 in

Force Related

Installation Torque Recommended in-lb	480 LBS/in
---------------------------------------	------------

General

Material Type - Screw Plated	DURIUM™ Silicon Bronze
Sub Brand	No
Product Type	MECHANICAL CONNECTOR
UPC	Mechanical
Type	781810260562
U Bolt Type	GP
Material	254
Plating Type	Copper Alloy
UPC 12 Digit	Unplated
UPC 14 Digit GTIN	781810260562
	00781810260562

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1000
Carton Quantity	20

Product Assets

[Catalog \[English\]](#)