



GRF4C3, Universal Grounding Clamp, 1 or 2 Conductors to Round or Square Pedestal

By Burndy
Catalog # [GRF4C3](#)

Universal Grounding Clamp, 1 or 2 Nos of Conductors, 8 AWG-2 AWG, Pedestal Type : 1" (Round), Upto 7/8" (Square), 3/8" Stud

Features

- One connector fits all applications
- Ease of specification and installation
- Single bolt design with no need to disassemble
- Single wrench installation
- Accepts 1 or 2 ground conductors
- Requires less connectors to install signal reference grid
- Tin plated cast bronze construction
- Resists corrosion and provides extended life ground connection
- Grounds all pedestals (round or square)
- Will accept up to 7/8" Square and up to 1" Round
- Serves 3 needs: Signal Reference Grid, Static Ground, Fault Current Ground
- UNIGROUND™ connector will solve all ground problems found in computer applications today
- UL467 Listed for the US and Canadian Markets

Application

For Raised Floor Systems

Specifications

Certification - UL Recognized	No
Certification - cULus	No
EU RoHS Indicator	Yes
Industry Standard(s)	UL467
Certification - ETL	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
Certification - UL Listed Direct Burial	No
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor - Pipe or Round Tube Size Range	3/8 in -1 in
Conductor - Pipe or Round Tube Size	• 3/8 • 1/2 • 3/4 • 1
Conductor - Pipe or Square Tube Size Range	1/2 in -7/8 in



Conductor - Pipe or Square Tube Size	• 1/2 • 5/8 • 3/4 • 7/8
Conductor - Copper Str Size	• 8 AWG • 7 AWG • 6 AWG • 5 AWG • 4 AWG • 3 AWG • 2 AWG
Conductor - Copper Solid Size	• 8 AWG • 7 AWG • 6 AWG • 5 AWG • 4 AWG • 3 AWG • 2 AWG
Number Of Conductors	• 1 • 2
Conductor - Copper Solid Size Range	8 AWG-2 AWG
Conductor - Copper Str Size Range	8 AWG-2 AWG

Dimensions

Package Height	0.000 in
Dimension - Height mm	79.8 mm
Dimension - Height inch	3.14 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - Width mm	45 mm
Dimension - Width inch	1.76 in
Dimension - B Length inch	1.96 in

Force Related

Installation Torque Recommended in-lb	100 LBS/in
---------------------------------------	------------

General

Trade Name	UNIGROUND™
Material - Hardware Plated	DURIUM™ Silicon Bronze Y
Pedestal Type	• Round • Square

Sub Brand	UNIGROUND
UPC	781810828021
Type	GRF
Material	Copper Alloy
Plating Type	Tin - Electro Plated
UPC 12 Digit	781810828021
UPC 14 Digit GTIN	00781810828021

Logistics

Pallet Quantity	2800
Carton Quantity	25

Product Assets

[Catalog \[English\]](#)



A Hubbell brand