



K11A30U, AL Universal Terminal, 2-Conductor, 1-Hole

By Burndy
Catalog # [K11A30U](#)

2 Conductors: 6 AWG-300 kcmil, 1 Hole, 5/16" Stud, 2 Screws,
AL/CU, Tin Plated

Features

- Dual rated panelboard lugs
- Constructed from high strength, extruded aluminum alloy
- Electro tin-plated to provide low contact resistance

Application


For Aluminum And Copper Conductors

Specifications

EU RoHS Indicator	Yes
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	EX
Certification - UL Listed Direct Burial	No
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - AL Str Size	• 6 AWG • 4 AWG • 3 AWG • 2 AWG • 1 AWG • 1/0 AWG • 2/0 AWG • 3/0 AWG • 4/0 AWG • 250 kcmil • 266 kcmil • 300 kcmil
Conductor - AL Str Size Range	6 Str.- 300 Kcmil
Conductor - Copper Str Size	• 6 AWG • 5 AWG • 4 AWG • 3 AWG • 2 AWG • 1 AWG • 1/0 • 2/0 AWG • 3/0 AWG • 4/0 AWG • 250 kcmil



Conductor Size	• 300 kcmil 6 AWG-300 KCMIL
Conductor - Copper Solid Size	• 4 AWG • 3 AWG • 2 AWG • 1 AWG • 1/0 AWG • 2/0 AWG • 3/0 AWG • 4/0 AWG
Number Of Conductors	2
Conductor - Copper Solid Size Range	4 AWG-4/0 AWG
Conductor Type	• AL C Str-Size • CU C Str-Size • CU C Solid-Size
Conductor - Copper Str Size Range	6 Str.- 300 Kcmil

Configuration

Physical Attribute - Number of Holes	1
Connector Type	Stacked

Dimensions

Dimension - Pad Width inch	1.02 in
Package Height	3.400 in
Dimension - Height mm	51.6 mm
Dimension - Height inch	2.03 in
Dimension - Height fraction	2 in
Package Weight	0.910 lb.
Package Length	4.300 in
Package Width	3.750 in
Dimension - L Length Overall mm	76 mm
Dimension - Thread Size	5/16 in
Dimension - Hole Size mm	8 mm
Dimension - Hole Size inch	0.33 in
Dimension - Screw Size inch	11/16
Dimension - Stud Size inch	5/16 in
Dimension - Stud Size fraction	5/16
Dimension - Bolt Hole Size inch	0.31 in
Dimension - Bolt Size fraction	5/16
Dimension - Width mm	25 mm
Dimension - Width inch	1.02 in
Dimension - D inch	0.94 in

Dimension - N inch	0.47 in	Hex Key	3/4
Dimension - Length Overall inch	3.00 in	Material	Aluminum
		Plating Type	Tin plated
		UPC 12 Digit	781810370261
		UPC 14 Digit GTIN	00781810370261
Force Related		Logistics	
Installation Torque Recommended in-lb	275 LBS/in	Pallet Quantity	2304
		Carton Quantity	72
General		Operational	
Material - Hardware	Aluminum	Temperature Rating	194
Physical Attribute - Screw Type	Allen		
Plated	Y		
Sub Brand	UNIVERSAL TERM		
UPC	781810370261		
Type	Bolted Lugs & Terminals		
		Product Assets	
		Catalog [English]	



A Hubbell brand