




K2C20B1, SERVIT POST Mechanical Connector, 2 Cables to Flat

By Burndy

Catalog # [K2C20B1](#)

SERVIT POST™ Mechanical Connector, 2 Cables to Flat



Features

- SERVIT POST™ mechanical connector used to ground 1 or 2 cables to steel structures, fence posts, and transformers
- Also used to tap 1 or 2 cables from bus bar
- 1-Wrench installation

Application


For Used To Ground One Or Two Copper Cables To Steel Structures, Fence Posts, Transformers, Tap One Or Two Cables From Bus Bar And Direct Burial

Specifications

Certification - UL Recognized	No
Certification - cULus	No
EU RoHS Indicator	Yes
Industry Standard(s)	UL467
Certification - ETL	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
Certification - UL Listed Direct Burial	Yes
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size	• 10 AWG • 9 AWG • 8 AWG • 7 AWG • 6 AWG • 5 AWG
Conductor - Copper Solid Size	• 10 AWG • 9 AWG • 8 AWG • 7 AWG • 6 AWG • 5 AWG • 4 AWG
Conductor - Copper Solid Size Range	10 AWG-4 AWG
Physical Attribute - Number of Conductors Accommodated	2
Total	



Conductor - Copper Str Size Range	10 AWG-5 AWG
-----------------------------------	--------------

Dimensions

Package Height	0.000 in
Dimension - Height mm	21.8 mm
Dimension - Height inch	0.86 in
Dimension - Height fraction	7/8
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - P inch	0.22 in
Dimension - L Length Overall mm	48.8 mm
Dimension - Nut Width inch	0.69 in
Dimension - Threads per inch	18
Dimension - Bolt Size fraction	5/16
Dimension - Body Width inch	0.50 in
Dimension - B Length fraction	27/32 in
Dimension - B Length inch	0.85 in
Dimension - D inch	1.00 in
Dimension - Length Overall inch	1.92 in

Force Related

Stud Installation Torque inch pounds	180 LBS/in
--------------------------------------	------------

General

Trade Name	SERVIT POST™
Plated	N
Sub Brand	SERVIT POST
UPC	781810257050
Type	KC and K2C Series
Material	Bronze Alloy, Leaded
Plating Type	Unplated
UPC 12 Digit	781810257050
UPC 14 Digit GTIN	00781810257050

Logistics

Pallet Quantity	19800
Carton Quantity	50

Product Assets

[Catalog \[English\]](#)