




K2C15, SERVIT POST Mechanical Connector, 2 Cables to Flat

By Burndy
Catalog # [K2C15](#)

SERVIT POST™ Mechanical Connector, 2 Cables to Flat



Features

- SERVIT POST™ mechanical connector used to ground 1 or 2 cables to steel structures, fence posts, and transformers
- Also used to tap 1 or 2 cables from bus bar
- 1-Wrench installation

Application

For Used To Ground One Or Two Copper Cables To Steel Structures, Fence Posts, Transformers, Tap One Or Two Cables From Bus Bar And Direct Burial

Specifications

Certification - UL Recognized	No
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	UL467
Certification - ETL	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance	EX
Status	
Certification - UL Listed Direct Burial	Yes
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size	• 12 AWG • 10 AWG • 9 AWG
Conductor - Copper Solid Size	• 12 AWG • 11 AWG • 10 AWG • 9 AWG • 8 AWG
Conductor - Copper Solid Size Range	8 AWG - 12 AWG
Physical Attribute - Number of Conductors Accommodated Total	2
Conductor - Copper Str Size Range	9 AWG - 12 AWG

Dimensions

Package Height	0.000 in
Dimension - Height mm	17.5 mm



A Hubbell brand

Dimension - Height inch	0.81 in
Dimension - Height fraction	5/8
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - P inch	0.14 in
Dimension - L Length Overall mm	30.2 mm
Dimension - Nut Width inch	0.50 in
Dimension - Threads per inch	20
Dimension - Bolt Size fraction	1/4
Dimension - Body Width inch	0.38 in
Dimension - B Length fraction	3/8 in
Dimension - Width inch	21 mm
Dimension - B Length inch	0.37 in
Dimension - D inch	0.50 in
Dimension - Length Overall inch	1.19 in

Force Related

Stud Installation Torque inch pounds	80 LBS/in
--------------------------------------	-----------

General

Product Family	Grounding and Bonding Connectors>Copper Mechanical Grounding Connectors>Cable(s) to Bar/Flat
Trade Name	SERVIT POST™
Plated	No
Sub Brand	SERVIT POST
Product Type	Mechanical
UPC	781810256800
Type	KC and K2C Series
Material	Bronze Alloy, Leaded
Plating Type	Unplated
UPC 12 Digit	781810256800
UPC 14 Digit GTIN	00781810256800

Logistics

Minimum Pack Quantity	1
Pallet Quantity	44550
Carton Quantity	50

Product Assets

[Catalog \[English\]](#)