



K3A26U2N, AL Universal Terminal, 3-Conductor, 2-Hole

By Burndy
Catalog # [K3A26U2N](#)

3-Conductor, 2-Hole, 1/2" Stud, 1.75" Spacing, #14-2/O AWG, Tin Plated

Features

- Dual rated lugs
- Constructed from high strength aluminum alloy
- Electro tin plating proving low contact resistance

Application

For Aluminum and Copper Conductors

Specifications

EU RoHS Indicator	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	EX
Certification - UL Listed Direct Burial	No
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - AL Str Size	• 8 AWG • 6 AWG • 4 AWG • 3 AWG • 2 AWG • 1 AWG • 1/O AWG • 2/O AWG
Conductor - AL Str Size Range	14 Str.-2/O AWG
Conductor - Copper Str Size	• 14 AWG • 12 AWG • 10 AWG • 9 AWG • 8 AWG • 7 AWG • 6 AWG • 5 AWG • 4 AWG • 3 AWG • 2 AWG • 1 AWG • 1/O • 2/O AWG
Conductor Size	14-2/O AWG



Number Of Conductors	3
Conductor Type	• AL C Str-Size • CU C Str-Size
Conductor - Copper Str Size Range	14 Str.-2/O AWG

Configuration

Physical Attribute - Number of Screws	3
Physical Attribute - Number of Holes	2
Connector Type	Parallel Set-Screw

Dimensions

Dimension - Pad Width inch	1.97 in
Package Height	3.450 in
Dimension - Height mm	45.5 mm
Dimension - Hole Size fraction	9/16
Dimension - Height inch	1.79 in
Dimension - Height fraction	1.8 in
Package Weight	1.250 lb.
Package Length	5.500 in
Package Width	4.750 in
Dimension - L Length Overall mm	95 mm
Dimension - Width fraction	1-19/20 in
Dimension - Hole Size mm	14 mm
Dimension - Hole Size inch	0.56 in
Dimension - Stud Size inch	1/2 in
Dimension - Bolt Hole Size inch	0.57 in
Dimension - Bolt Size fraction	1/2
Dimension - Width mm	50 mm
Dimension - Width inch	1.97 in
Dimension - D inch	3.06 in
Dimension - N inch	0.63 in
Dimension - Length Overall inch	3.75 in

Force Related

Installation Torque Recommended in-lb	50 LBS/in
---------------------------------------	-----------

General

Material - Hardware	Aluminum
Physical Attribute - Screw Type	Slot

Plated	Y
Sub Brand	UNIVERSAL TERM
UPC	781810601051
Type	Bolted Lugs & Terminals
Material	Aluminum
Plating Type	Tin plated
UPC 12 Digit	781810601051
UPC 14 Digit GTIN	00781810601051

Pallet Quantity	3456
Carton Quantity	108

Operational

Temperature Rating	194
--------------------	-----

Product Assets

Catalog [\[English\]](#)

Logistics



A Hubbell brand