



K3A2U4, AL Universal Terminal, 3-Conductor, 4-Hole

By Burndy
Catalog # [K3A2U4](#)

3-Conductor, 4-Hole, 5/16" Stud, .88" Spacing, #14-2 AWG, Tin Plated, Dual Rated

Features

- Dual rated lugs
- Constructed from high strength aluminum alloy
- Electro tin plating proving low contact resistance

Specifications

Certification - cULus	No
Certification - UL Recognized	No
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	EX
Certification - CSA Approved	Yes
UL Listed	Yes
Certification - UL Listed Direct Burial	No

Conductor

Conductor - Copper Str Size	• 14 AWG • 12 AWG • 10 AWG • 9 AWG • 8 AWG • 7 AWG • 6 AWG • 5 AWG • 4 AWG • 3 AWG • 2 AWG
Conductor - AL Str Size	• 8 AWG • 6 AWG • 4 AWG • 3 AWG • 2 AWG
Conductor - AL Str Size Range	14-2 AWG
Number Of Conductors	3
Conductor Size	14-2 AWG
Conductor - Copper Str Size Range	14-2 AWG
Conductor Type	• AL C Str-Size • CU C Str-Size

Configuration



Physical Attribute - Number of Holes	4
Physical Attribute - Number of Screws	3
Connector Type	Parallel Set-Screw

Dimensions

Package Length	0.000 in
Package Width	0.000 in
Dimension - F Width Center to Center inch	0.88 in
Package Weight	0.000 lb.
Dimension - L Length Overall mm	55.62 mm
Dimension - Pad Width inch	1.64 in
Dimension - Height fraction	5/8 in
Dimension - Height inch	0.62 in
Package Height	0.000 in
Dimension - Height mm	15.7 mm
Dimension - Hole Size fraction	11/32
Dimension - Hole Size inch	0.34 in
Dimension - Hole Size mm	9 mm
Dimension - Stud Size inch	5/16 in
Dimension - Width fraction	1-59/100 in
Dimension - Width inch	1.64 in
Dimension - Width mm	40 mm
Dimension - Bolt Hole Size inch	0.57 in
Dimension - Bolt Size fraction	5/16
Dimension - Length Overall inch	2.19 in
Dimension - D inch	1.63 in
Dimension - N inch	0.34 in

Force Related

Installation Torque Recommended in-lb	50 LBS/in
---------------------------------------	-----------

General

Material - Hardware	Aluminum
Physical Attribute - Screw Type Plated	Slot Y
Type	Bolted Lugs & Terminals
UPC 12 Digit	781810370377
UPC 14 Digit GTIN	00781810370377
Material	Aluminum
Plating Type	Tin plated

UPC781810370377

Logistics

Minimum Pack Quantity	96
Carton Quantity	6
Pallet Quantity	390



A Hubbell brand

Operational

Temperature Rating194

Product Assets

[Catalog \[English\]](#)