



KA39U30UNT, AL Universal Terminal, 1/2" Stud, Dual Rated

By Burndy
Catalog # [KA39U30UNT](#)

Accommodates 1 Conductor 1/0 Str-750 kcmil AL/CU, or 2
Conductors 1/0 Str-300 kcmil AL/CU

Features


- AL Universal Terminal
- Tin Plated

Specifications

Certification - UL Recognized	No
Certification - cULus	No
Certification - ETL	No
Standards - RoHS Compliance Status	EX
UL Listed	No
Certification - CSA Approved	Yes

Conductor

Conductor - AL Str Size	• 1/0 AWG • 2/0 AWG • 3/0 AWG • 4/0 AWG • 250 kcmil • 266 kcmil • 300 kcmil • 336 kcmil • 350 kcmil • 397 kcmil • 400 kcmil • 450 kcmil • 477 kcmil • 500 kcmil • 550 kcmil • 556 kcmil • 600 kcmil • 636 kcmil • 650 kcmil • 700 kcmil
Conductor - AL Str Size Range	1/0 AWG-700 kcmil
Conductor - Copper Str Size	• 1/0 • 2/0 AWG • 3/0 AWG • 4/0 AWG • 250 kcmil • 300 kcmil • 350 kcmil • 400 kcmil • 450 kcmil • 500 kcmil



Conductor Type	• 550 kcmil • 600 kcmil • 700 kcmil • CU C Str-Size • AL C Str-Size • CU C Solid-Size
Conductor - Copper Str Size Range	1/0 -700 kcmil

Configuration

Physical Attribute - Number of Screws	1
Physical Attribute - Number of Holes	1

Dimensions

Dimension - Pad Width inch	1.30 in
Package Height	0.000 in
Dimension - Height mm	46.5 mm
Dimension - Height inch	1.83 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	71 mm
Width	1.3 in
Dimension - Hole Size mm	13 mm
Dimension - Hole Size inch	0.52 in
Length	2.81 in
Height	1.83 in
Dimension - D inch	1.50 in
Dimension - N inch	0.64 in
Dimension - Length Overall inch	2.81 in
Dimensions	2.81 in x 1.3 in x 1.83 in

Force Related

Installation Torque Recommended in-lb	500 LBS/in
---------------------------------------	------------

General

Material - Hardware	Aluminum
Physical Attribute - Screw Type	Allen
Plated	Y
UPC	781810236956

Type	Bolted Lugs & Terminals	Minimum Pack Quantity	350
Material	Aluminum	Pallet Quantity	144
Plating Type	Tin	Carton Quantity	30
UPC 14 Digit GTIN	00781810236956		

Logistics

Product Assets

[Catalog \[English\]](#)



A Hubbell brand