



KA4C, Copper Mechanical Terminal, 1-Hole

By Burndy
Catalog # [KA4C](#)

Compact Copper Terminal, 1 Hole, 14 AWG (Sol)-4 AWG (Str),
1/4" Stud, 1 Screw



Features

- Compact, high copper alloy terminal for joining cable to equipment pads or terminal blocks

Application

For Joining A Wide Range Of Copper Cable To Equipment Pads Or Terminal Blocks

Specifications

Certification - UL Recognized	No
Certification - cULus	No
EU RoHS Indicator	Yes
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	EX
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size	• 14 AWG • 12 AWG • 10 AWG • 9 AWG • 8 AWG • 7 AWG • 6 AWG • 5 AWG • 4 AWG
Conductor Size	14-4 AWG
Conductor - Copper Solid Size	• 14 AWG • 13 AWG • 12 AWG • 11 AWG • 10 AWG • 9 AWG • 8 AWG • 7 AWG • 6 AWG • 5 AWG • 4 AWG
Conductor - Copper Solid Size Range	14 AWG-4 AWG

Conductor Type	• CU C Str-Size • AL C Str-Size
Conductor - Copper Str Size Range	14 AWG-4 AWG

Configuration

Physical Attribute - Number of Screws	1
Physical Attribute - Number of Holes	1
Connector Type	Terminal

Dimensions

Dimension - Pad Width inch	0.54 in
Package Height	4.500 in
Dimension - Height mm	19.6 mm
Dimension - Hole Size fraction	9/32
Dimension - Height inch	0.77 in
Dimension - Height fraction	3/4
Package Weight	3.210 lb.
Package Length	5.000 in
Package Width	4.000 in
Dimension - L Length Overall mm	28 mm
Dimension - Hole Size mm	7 mm
Dimension - Hole Size inch	0.28 in
Dimension - Stud Size inch	1/4
Dimension - Bolt Size fraction	1/4
Dimension - B Length fraction	8/17 in
Dimension - B Length inch	0.47 in
Dimension - N inch	0.25 in
Dimension - Length Overall inch	1.11 in

Force Related

Installation Torque Recommended in-lb	45 LBS/in
---------------------------------------	-----------

General

Material - Hardware	Steel
Physical Attribute - Screw Type	Slot
Plated	N
Sub Brand	KA-LUG
UPC	781810361405
Type	Bolted Lugs & Terminals

Material	Copper	Pallet Quantity	48000
Plating Type	Unplated	Carton Quantity	1000
Hardware Type	5 / 16 "	Product Assets	
UPC 14 Digit GTIN	00781810361405		
Logistics		Catalog [English]	

