



KK3A44U4N, AL Universal Terminal, 3-Conductor, 4-Hole

By Burndy

Catalog # [KK3A44U4N](#)

Aluminum Universal Terminal, 3 Conductor, 4 Hole, 500-1000 kcmil, 1/2" Stud, 1.75" Stud Hole Spacing, 6 Screws, Al/Cu Rated, Tin Plated

Features

- Dual rated panelboard lugs constructed from high strength extruded aluminum alloy , electro tin-plated to provide low contact resistance

Specifications

Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	NC
Certification - UL Listed Direct Burial	No
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Number Of Wires	3
Conductor - AL Str Size	• 500 kcmil • 550 kcmil • 556 kcmil • 600 kcmil • 636 kcmil • 650 kcmil • 700 kcmil • 715 kcmil • 750 kcmil • 795 kcmil • 800 kcmil • 874 kcmil • 900 kcmil • 954 kcmil • 1000 kcmil
Conductor - AL Str Size Range	500 - 1000 Kcmil
Conductor Size	500-1000 KCMIL
Number Of Conductors	3
Conductor Type	• CU C Str-Size • AL C Str-Size
Conductor - Copper Str Size Range	500 - 1000 Kcmil

Configuration



Physical Attribute - Number of Holes	4
Connector Type	Parallel Set-Screw

Dimensions

Dimension - Pad Width inch	4.77 in
Package Height	0.000 in
Dimension - Height mm	48.3 mm
Dimension - Hole Size fraction	9/16
Dimension - Height inch	1.90 in
Package Weight	0.000 lb.
Package Length	0.000 in
Dimension - E Spacing between Holes fraction	1-3/4 in
Dimension - F Width Center to Center inch	1.75 in
Package Width	0.000 in
Dimension - L Length Overall mm	157 mm
Dimension - Hole Size mm	14 mm
Dimension - Hole Size inch	0.56 in
Dimension - Stud Size inch	0.56 in
Dimension - Bolt Hole Size inch	0.56 in
Dimension - Bolt Size fraction	1/2
Dimension - N inch	0.63 in
Dimension - Length Overall inch	6.19 in

General

Material - Hardware	Aluminum
Plated	Y
UPC	781810601075
Type	Bolted Lugs & Terminals
Material	Aluminum
Plating Type	Tin Plated
UPC 14 Digit GTIN	00781810601075

Logistics

Minimum Pack Quantity	5
Pallet Quantity	1
Carton Quantity	12

Product Assets

[Catalog \[English\]](#)