




KLU35TP, Cu Mechanical, Offset Tongue, Range Taking, 1-Hole

By Burndy
Catalog # [KLU35TP](#)



Copper Terminal, Offset Tongue, 1-Hole, 14 AWG (Sol)-6 AWG (Str), #10 Stud, Tin Plated

Features

- Range-taking design reduces SKUs required in inventory
- High conductivity copper alloy for long lasting reliable contact
- Compact design, easy to install
- Slot Robertson screw, hex head, hex socket bolt require no special installation tools

Specifications

Certification - UL Recognized	No
Certification - cULus	Yes
Industry Standard(s)	UL467
Certification - ETL	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance	CM
Status	
Certification - UL Listed Direct Burial	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size	• 14 AWG • 12 AWG • 10 AWG • 9 AWG • 8 AWG • 7 AWG • 6 AWG
Conductor Size	14-6 AWG
Conductor - Copper Solid Size	• 14 AWG • 13 AWG • 12 AWG • 11 AWG • 10 AWG • 9 AWG • 8 AWG • 7 AWG • 6 AWG
Conductor - Copper Solid Size Range	14 AWG-6 AWG
Conductor Type	• CU C Solid-Size • CU C Str-Size
Conductor - Copper Str Size Range	14 AWG-6 AWG

Configuration

Physical Attribute - Number of Screws	1
Physical Attribute - Number of Holes	1
Connector Type	Pressure Bar

Dimensions

Dimension - Pad Width inch	0.39 in
Package Height	0.000 in
Dimension - Height mm	0 mm
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	31 mm
Dimension - Hole Size mm	5 mm
Dimension - Hole Size inch	0.20 in
Dimension - Screw Size inch	1/4
Dimension - Strip Length inch	5/8
Dimension - Stud Size inch	#10
Dimension - Bolt Size fraction	#10
Dimension - B Length fraction	7/16 in
Dimension - B Length inch	0.43 in
Dimension - N inch	0.22 in
Dimension - Length Overall inch	1.24 in

Force Related

Installation Torque Recommended in-lb	35
---------------------------------------	----

General

Product Family	MECHANICAL
Trade Name	SCRULUG™
Physical Attribute - Screw Type	Slot
Plated	Yes
Product Type	Terminal
UPC	781810352557
Type	Bolted Lugs & Terminals
Material	Copper
Plating Type	Tin
Hardware Type	1/4 UNF Slotted SetScrew
UPC 14 Digit GTIN	00781810352557

Logistics

Minimum Pack Quantity	5000
Pallet Quantity	18560

