



KLU225TP, Cu Terminal, Offset Tongue, Range Taking, 1-Hole

By Burndy

Catalog # [KLU225TP](#)

Copper Terminal, Offset Tongue, 1-Hole, 5/16" Stud, #2-4/0 AWG,
Tin Plated



Features

- Range-taking design reduces SKUs required in inventory
- High conductivity copper alloy for long lasting reliable contact
- Compact design, easy to install
- Slot Robertson screw, hex head, hex socket bolt require no special installation tools

Specifications

Certification - UL Recognized	No
Buy American Compliant	Contact Manufacturer
Certification - cULus	Yes
EU RoHS Indicator	Contact Manufacturer
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	UL467
Certification - ETL	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
Certification - UL Listed Direct Burial	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size	• 2 AWG • 1 AWG • 1/0 • 2/0 AWG • 3/0 AWG • 4/0 AWG
Conductor Size	2-4/0 AWG
Conductor Type	CU C Str-Size
Conductor - Copper Str Size Range	2 AWG-4/0 AWG

Configuration

Physical Attribute - Number of Screws	1
Physical Attribute - Number of Holes	1
Connector Type	Pressure Bar

Dimensions



A Hubbell brand

Dimension - Pad Width inch	0.99 in
Package Height	0.000 in
Dimension - Height mm	0 mm
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	65 mm
Dimension - Hole Size mm	9 mm
Dimension - Hole Size inch	0.34 in
Dimension - Screw Size inch	7/16
Dimension - Strip Length inch	1-5/16
Dimension - Stud Size inch	5/16
Dimension - Bolt Size fraction	5/16
Dimension - B Length fraction	15/16 in
Dimension - B Length inch	0.94 in
Dimension - N inch	0.51 in
Dimension - Length Overall inch	2.55 in

Force Related

Installation Torque	120
Recommended in-lb	

General

Trade Name	SCRULUG™
Physical Attribute - Screw Type Plated	Allen Y
Sub Brand	SCRULUG
UPC	781810352755
Type	KLU
Construction Material - Main Material	Copper Alloy Copper
Plating Type	Tin
Hardware Type	7/16 UNF Socket/HexScrew
UPC 14 Digit GTIN	00781810352755

Logistics

Minimum Pack Quantity	1000
Pallet Quantity	8700
Carton Quantity	25

Product Assets

[Catalog \[English\]](#)