



KPA28, Pressure Bar Cu Lug, 1-Hole, Tin Plated

By Burndy
Catalog # [KPA28](#)

Cu Terminal with Pressure Bar, 1-Hole, 3/8" Stud, 1/0-4/0 AWG,
Tin Plated



Features

- High copper alloy terminal (tin-plated) for joining a wide range of cable to equipment pads or terminal blocks
- Tongue and body are 1-piece design, pressure bar equalizes pressure over the conductor and prevents the screw from cutting into the cable

Application

For Joining A Wide Range Of Cable To Equipment Pads Or Terminal Blocks, Especially Good In Light Industrial Applications

Specifications

Certification - UL Recognized	No
Certification - cULus	No
EU RoHS Indicator	Yes
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
Certification - UL Listed Direct Burial	No
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Copper Str Size	• 1/0 • 2/0 AWG • 3/0 AWG • 4/0 AWG
Conductor Size	1/0-4/0 AWG
Conductor - Copper Str Navy Size Range	125 (61) Navy-150 (61) Navy
Conductor - Copper Str Navy Size	• 125 (61) Navy • 150 (61) Navy
Conductor Type	• CU C Str-Size • CU C Navy-Size
Conductor - Copper Str Size Range	1/0 -4/0 AWG

Configuration

Physical Attribute - Number of Screws	1
---------------------------------------	---

Physical Attribute - Number of Holes	1
Connector Type	Pressure Bar

Dimensions

Dimension - Pad Width inch	0.97 in
Package Height	0.000 in
Dimension - Height mm	42.2 mm
Dimension - Height inch	1.66 in
Dimension - Height fraction	1-21/32 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	61 mm
Dimension - Hole Size mm	10 mm
Dimension - Hole Size inch	0.39 in
Dimension - Stud Size inch	3/8
Dimension - Bolt Size fraction	3/8
Dimension - D inch	1.12 in
Dimension - N inch	0.53 in
Dimension - Length Overall inch	2.40 in

Force Related

Installation Torque	250
Recommended in-lb	

General

Trade Name	SCRULUG™
Physical Attribute - Screw Type	Hexagonal Bolt
Plated	Y
Sub Brand	SCRULUG
UPC	781810355909
Type	Bolted Lugs & Terminals
Material	Copper
Plating Type	Tin
UPC 14 Digit GTIN	00781810355909

Logistics

Pallet Quantity	8700
Carton Quantity	25

Product Assets

[Catalog \[English\]](#)



A Hubbell brand