



KPA25UNPL, Pressure Bar Cu Lug, 1-Hole, Unplated

By Burndy

Catalog # [KPA25UNPL](#)

Cu Terminal with Pressure Bar, 1-Hole, 5/16" Stud, #4-1/0 Str, Unplated



Features

- High copper alloy terminal (unplated) for joining a wide range of cable to equipment pads or terminal blocks
- Tongue and body are 1-piece design, pressure bar equalizes pressure over the conductor and prevents the screw from cutting into the cable

Specifications

Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
Certification - UL Listed Direct Burial	No
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Copper Str Size	• 4 AWG • 3 AWG • 2 AWG • 1 AWG • 1/0
Conductor Size	4-1/0 AWG
Conductor - Copper Str Navy Size Range	50 (19) Navy-100 (61) Navy
Conductor - Copper Str Navy Size	• 50 (19) Navy • 60 (37) Navy • 75 (37) Navy • 100 (61) Navy
Conductor Type	• CU C Str-Size • CU C Navy-Size
Conductor - Copper Str Size Range	4 AWG-1/0

Configuration

Physical Attribute - Number of Screws	1
Physical Attribute - Number of Holes	1



Connector Type	Pressure Bar
----------------	--------------

Dimensions

Dimension - Pad Width inch	0.75 in
Package Height	0.000 in
Dimension - Height mm	31.8 mm
Dimension - Height inch	1.25 in
Dimension - Height fraction	1-1/4 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	46 mm
Dimension - Hole Size mm	8 mm
Dimension - Hole Size inch	0.33 in
Dimension - Stud Size inch	5/16
Dimension - Bolt Size fraction	5/16
Dimension - D inch	0.81 in
Dimension - N inch	0.41 in
Dimension - Length Overall inch	1.82 in

Force Related

Installation Torque	180
Recommended in-lb	

General

Trade Name	SCRULUG™
Physical Attribute - Screw Type	Hexagonal Bolt
Plated	N
UPC	781810172704
Type	Bolted Lugs & Terminals
Material	Copper
Plating Type	Unplated
UPC 14 Digit GTIN	00781810172704

Logistics

Minimum Pack Quantity	10
Pallet Quantity	17400
Carton Quantity	100

Product Assets

[Catalog \[English\]](#)