




KS173, Split Bolt Connector, Run/Tap: #8 AWG Str-#6 AWG Sol

By Burndy
Catalog # [KS173](#)



Copper Split Bolt, Cu: 8 AWG (Str)-6 AWG (Sol) (Run & Tap)

Features

- Compact, high-strength, copper alloy with free-running threads and easy to grip wrench flats
- Highly resistant to cracking and corrosion

Application

For Copper, Copperweld, Direct Burial Cables

Specifications

Certification - UL Recognized	No
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
Buy America(n) Qualified	BABA Compliant (All status valid till December 2026)
Industry Standard(s)	RUS
Certification - ETL	No
Standards - Industry Standards Met	RUS
Standards - RoHS Compliance	CM
Status	
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Run Range	8 STR - 6 STR
Conductor - Copper Str Run	• 8 AWG • 7 AWG • 6 AWG
Conductor - Copper Solid Run Range	6 AWG
Conductor - Copper Solid Run	6 AWG
Conductor - Copper Solid Tap	6 AWG
Conductor - CopperWeld Solid Size Range	12 AWG-6 AWG
Conductor - CopperWeld C Solid Size	• 12 AWG • 10 AWG • 9 AWG • 8 AWG • 7 AWG • 6 AWG
Conductor - CopperWeld Str Tap Range	8 D AWG-6 A AWG
Conductor - CopperWeld Str Tap	• 8 D AWG • 7 A AWG • 7 D AWG • 6 A AWG

Conductor Type

- CU C Solid-Run
- CU C Str-Run
- CU Weld C Solid-Run
- CU Weld C Str-Run
- CU C Str-Tap
- CU Weld C Solid-Tap
- CU Weld C Str-Tap

Conductor - Copper Str Tap Range

Conductor - Copper Str Tap

- 8 STR - 6 STR
- 16 AWG
 - 14 AWG
 - 12 AWG
 - 10 AWG
 - 9 AWG
 - 8 AWG
 - 7 AWG
 - 6 AWG

Configuration

Connector Type	Split Bolt
----------------	------------

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	25 mm
Width	0.7 in
Dimension - Width mm	18 mm
Dimension - Width inch	0.70 in
Dimension - Cross Flats inch	.62 in
Dimension - Length Overall inch	0.98

Force Related

Installation Torque Recommended in-lb	165 LBS/in
---------------------------------------	------------

General

Product Family	Power Connectors>Split Bolts>KS
Trade Name	SERVIT®
Plated	No
Sub Brand	SERVIT
Product Type	Mechanical
UPC	781810021507
Type	KS-3
Material	Copper

Plating Type	Unplated	Pallet Quantity	39600
UPC 12 Digit	781810021507	Carton Quantity	100
UPC 14 Digit GTIN	00781810021507		

Logistics

Minimum Pack Quantity1

Product Assets

[Catalog \[English\]](#)

