



KPA28G1, Pressure Bar Cu Lug, 1-Hole, Tin Plated

By Burndy
Catalog # [KPA28G1](#)

Mechanical Pressure Bar Style Copper Lug, 1-Hole, 1/2" Stud, 1/0-4/0 Str, Tin Plated



Features

- High copper alloy terminal (tin-plated) for joining a wide range of cable to equipment pads or terminal blocks
- Tongue and body are 1-piece design, pressure bar equalizes pressure over the conductor and prevents the screw from cutting into the cable

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	UI
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Navy Size Range	125 (61) Navy-150 (61) Navy
Conductor - Copper Str Navy Size	• 125 (61) Navy • 150 (61) Navy
Conductor - Copper Str Size Range	1/0 -4/0 AWG
Conductor - Copper Str Size	• 1/0 • 2/0 AWG • 3/0 AWG • 4/0 AWG

Configuration

Physical Attribute - Number of Screws	1
Physical Attribute - Number of Holes	1
Connector Type	Terminal

Current

Rating - Minimum Voltage	600
--------------------------	-----

Dimensions

Dimension - Pad Width inch	0.97 in
Package Height	0.000 in

Dimension - Height mm	42.2 mm
Dimension - Height inch	1.66 in
Dimension - Height fraction	1-3/5 in
Package Weight	0.000 lb.
Dimension - Width mm	22 mm
Dimension - Width inch	0.88 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	58 mm
Dimension - D inch	1.12 in
Dimension - N inch	0.53 in
Dimension - Hole Size mm	13 mm
Dimension - Hole Size inch	0.53 in
Dimension - Length Overall inch	2.30 in

Force Related

Installation Torque Recommended in-lb	250 LBS/in
---------------------------------------	------------

General

Physical Attribute - Screw Type	Hexagonal Bolt
Plated	Y
Trade Name	SCRULUG™
UPC	781810242506
Type	Bolted Lugs & Terminals
Material	Copper
Plating Type	Tin
UPC 12 Digit	781810242506
UPC 14 Digit GTIN	00781810242506

Logistics

Minimum Pack Quantity	1
Pallet Quantity	8700
Carton Quantity	25

Operational

Temperature Rating	194
--------------------	-----

Product Assets

[Catalog \[English\]](#)



A Hubbell brand