



KPA8CUNPL, Mech. Terminal for Copper, 1-Hole, Unplated

By Burndy
Catalog # [KPA8CUNPL](#)

Mech. Pressure Bar Style Copper, 1-Hole, #10 Stud, #14 Sol-8 Str, Unplated



Features

- High copper alloy terminal (unplated) for joining a wide range of cable to equipment pads or terminal blocks
- Tongue and body are 1-piece design, pressure bar equalizes pressure over the conductor and prevents the screw from cutting into the cable

Specifications

Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
Certification - UL Listed Direct Burial	No
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Copper Str Size	• 14 AWG • 12 AWG • 10 AWG • 9 AWG • 8 AWG
Conductor Size	14-8 AWG
Conductor - Copper Str Navy Size Range	4 (1) Navy-14 (140) Navy
Conductor - Copper Str Navy Size	• 4 (1) Navy • 4 (7) Navy • 4 (19) Navy • 4 (41) Navy • 6 (7) Navy • 6 (19) Navy • 9 (7) Navy • 9 (37) Navy • 14 (7) Navy • 14 (140) Navy
Conductor - Copper Solid Size	• 14 AWG • 13 AWG • 12 AWG • 11 AWG • 10 AWG

Conductor - Copper Solid Size Range	• 9 AWG • 8 AWG 14 AWG-8 AWG
Conductor Type	• CU C Str-Size • CU C Solid-Size
Conductor - Copper Str Size Range	14 AWG-8 AWG

Configuration

Physical Attribute - Number of Screws	1
Physical Attribute - Number of Holes	1
Connector Type	Pressure Bar

Dimensions

Dimension - Pad Width inch	0.38 in
Package Height	0.000 in
Dimension - Height mm	18.3 mm
Dimension - Height inch	0.72 in
Dimension - Height fraction	18/25 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	24 mm
Dimension - Hole Size mm	5 mm
Dimension - Hole Size inch	0.21 in
Dimension - Bolt Size fraction	#10
Dimension - Width mm	10 mm
Dimension - Width inch	0.38 in
Dimension - D inch	0.47 in
Dimension - N inch	0.22 in
Dimension - Length Overall inch	0.95 in

Force Related

Installation Torque Recommended in-lb	25
---------------------------------------	----

General

Trade Name	SCRULUG™
Physical Attribute - Screw Type Plated	Slot N

UPC	781810006238
Type	Bolted Lugs & Terminals
Material	Copper
Plating Type	Unplated
UPC 14 Digit GTIN	00781810006238

Logistics	
Minimum Pack Quantity	1
Carton Quantity	1000

Product Assets

[Catalog \[English\]](#)



A Hubbell brand