



KVSW28, Mechanical Connector with Spacer Bar

By Burndy
Catalog # [KVSW28](#)

Mechanical Connector For CUWeld and Copper Supplied with a CU alloy Spacer that separates run and tap conductors, Run: 1/0 str. - 4/0 str., Tap: 6 sol. - 4/0 str.

Features

- Compact, 2-piece, high strength, high copper alloy, recommended for heavy duty connections
- High copper alloy spacer bar separates run and tap conductors
- Provides high contact pressure, confines conductor strands and assures vibration-proof connection
- Longer peened bolt permits swivel action for easier installation
- Neoprene rings hold silicon bronze bolts in place during installation
- Installed with ordinary wrench

Application

For Copper And Copperweld Conductors

Specifications

Certification - UL Recognized	No
Buy American Compliant	No
Certification - cULus	No
EU RoHS Indicator	Yes
Buy America(n) Qualified	TAA Compliant (All status valid till December 2026)
Certification - ETL	No
Standards - RoHS Compliance Status	EX
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Run Range	1/0 str. - 4/0 str.
Conductor - Copper Str Run	• 1/0 • 2/0 AWG • 3/0 AWG • 4/0 AWG
Conductor - Copper Solid Tap Range	6 AWG-4/0 AWG
Conductor - Copper Solid Tap	• 6 AWG • 5 AWG • 4 AWG • 3 AWG • 2 AWG • 1 AWG



Conductor Type	CU C Str-Size
Conductor - Copper Str Tap Range	6 sol. - 4/0 str.
Conductor - Copper Str Tap	• 1/0 AWG • 2/0 AWG • 3/0 AWG • 4/0 AWG • 6 AWG • 5 AWG • 4 AWG • 3 AWG • 2 AWG • 1 AWG • 1/0 • 2/0 AWG • 3/0 AWG • 4/0 AWG

Dimensions

Package Height	0.000 in
Dimension - Height mm	63.50 mm
Dimension - Height inch	2.50 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - Stud Size inch	3/8 in
Dimension - Width inch	1.67 in
Dimension - Length Overall inch	1.04 in

Force Related

Installation Torque Recommended in-lb	240 LBS/in
---------------------------------------	------------

General

Trade Name	OKLIP™
Plated	N
Sub Brand	OKLIP
UPC	781810066553
Type	KVSW
Material	Copper
Plating Type	Unplated
UPC 12 Digit	781810066553
UPC 14 Digit GTIN	00781810066553

Logistics

Minimum Pack Quantity	1
Pallet Quantity	3375

Carton Quantity25

Product Assets

[Catalog \[English\]](#)



A Hubbell brand