


N2AH2934N, Substation - Copper Terminal

By Burndy

Catalog # [N2AH2934N](#)

Substation Connectors



Features

- Type N2AH Bolted Terminals for 2 Copper Cables to Pad
- High copper alloy reversible cap terminal for joining a wide range of cables to pads
- Tongue is side formed to provide adequate clearance
- Terminal is designed for one-wrench installation

- 3/0 AWG
- 4/0 AWG
- 250 kcmil

Application

Substation

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	EX
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Solid Size	• 6 AWG • 5 AWG • 4 AWG • 3 AWG • 2 AWG • 1 AWG • 1/0 AWG • 2/0 AWG • 3/0 AWG • 4/0 AWG
Number Of Conductors	2
Conductor - Connection Combination	Cable to Flat
Conductor - Copper Solid Size Range	6 AWG-4/0 AWG
Conductor - Copper Str Size Range	6 AWG-250 kcmil
Conductor - Copper Str Size	• 6 AWG • 5 AWG • 4 AWG • 3 AWG • 2 AWG • 1 AWG • 1/0 • 2/0 AWG

Configuration

Physical Attribute - Pad Orientation	Offset
Physical Attribute - Pad Configuration	3 x 3 - 4 holes
Connector Type	Terminal

Dimensions

Dimension - Pad Width inch	3.00 in
Package Height	0.000 in
Dimension - Height mm	0 mm
Dimension - Hole Size fraction	9/16
Physical Attribute - Tongue Angle	Straight
Package Weight	0.000 lb.
Dimension - Width mm	124 mm
Dimension - Width inch	4.88 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	149 mm
Dimension - B Length inch	2.62 in
Dimension - D inch	3.00 in
Dimension - N inch	0.62 in
Dimension - Length Overall inch	5.87 in

Force Related

Installation Torque Recommended in-lb	480
---------------------------------------	-----

General

Plated	N
Material - Hardware	DURIUM™ Silicon Bronze
One Wrench Installation	Y
UPC	781810232217
Material	Copper Alloy
Plating Type	Unplated
UPC 12 Digit	781810232217
UPC 14 Digit GTIN	00781810232217

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1

Carton Quantity1

Product Assets

[Catalog \[English\]](#)



A Hubbell brand