


Substation - Copper Terminal

By Burndy

Catalog # [NAH3434N](#)

Cast Copper alloy terminal, 1/0 Sol.-500 kcmil, Cable to Pad



Application

Substation

Specifications

Certification - UL Recognized	No
Certification - cULus	No
EU RoHS Indicator	Contact Manufacturer
Certification - ETL	No
Standards - RoHS Compliance Status	EX
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size	1/0 2/0 AWG 3/0 AWG 4/0 AWG 250 kcmil 300 kcmil 350 kcmil 400 kcmil 450 kcmil 500 kcmil
Conductor - Copper Solid Size	1/0 AWG 2/0 AWG 3/0 AWG 4/0 AWG
Number Of Conductors	1
Conductor - Connection Combination	Cable to Flat
Conductor - Copper Solid Size Range	1/0 AWG-4/0 AWG
Conductor Type	- CU C Str-Size - CU C Solid-Size
Conductor - Copper Str Size Range	1/0 -500 kcmil

Configuration

Physical Attribute - Pad Orientation	Straight
Physical Attribute - Pad Configuration	3 x 3 - 4 holes
Physical Attribute - Pad Alignment	Offset

Physical Attribute - Number of Holes 4

Connector Type Terminal

Dimensions

Dimension - Pad Size inch	3 x 3
Dimension - Pad Width inch	3.00 in
Package Height	0.000 in
Dimension - Height mm	60.5 mm
Dimension - Hole Size fraction	9/16
Dimension - Height inch	2.38 in
Dimension - Height fraction	2-3/10 in
Package Weight	0.000 lb.
Package Length	0.000 in
Dimension - F Width Center to Center inch	1.75 in
Package Width	0.000 in
Dimension - L Length Overall mm	149 mm
Dimension - Width fraction	2-14/25 in
Dimension - Hole Size inch	0.56 in
Dimension - B Length fraction	2-31/50 in
Dimension - Width mm	65 mm
Dimension - Width inch	2.56 in
Dimension - B Length inch	2.62 in
Dimension - D inch	3.00 in
Dimension - N inch	0.62 in
Dimension - Length Overall inch	5.88 in

General

Material - Hardware	DURIUM™ Silicon Bronze
One Wrench Installation	Y
Plated	N
Sub Brand	SUBSTATION CONNECTOR
Clamping Element Design	Body and Cap
UPC	781810002247
Type	NAH
Material	Copper Alloy
Plating Type	Unplated
UPC 12 Digit	781810002247
UPC 14 Digit GTIN	00781810002247

Logistics

Carton Quantity 4



A Hubbell brand