


Substation - Copper Terminal

By Burndy

Catalog # [NAS292NTN](#)

Substation Connectors



Application

Substation

Specifications

Certification - UL Recognized	No
Certification - cULus	No
Certification - ETL	No
Standards - RoHS Compliance Status	EX
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Large Groove Min	2/0 str
Conductor - Large Groove Max	250 kcmil
Conductor - Copper Str Size	• 6 AWG • 5 AWG • 4 AWG • 3 AWG • 2 AWG • 1 AWG • 1/0 • 2/0 AWG • 3/0 AWG • 4/0 AWG • 250 kcmil
Conductor - Small Groove Min	6 sol
Conductor - Small Groove Max	1/0 str
Conductor - Copper Solid Size	• 6 AWG • 5 AWG • 4 AWG • 3 AWG • 2 AWG • 1 AWG • 1/0 AWG • 2/0 AWG • 3/0 AWG • 4/0 AWG
Number Of Conductors	1
Conductor - Connection Combination	Cable to Flat
Conductor - Copper Solid Size Range	6 AWG-4/0 AWG
Conductor Type	• CU C Str-Size • CU C Solid-Size

Conductor - Copper Str Size Range 6 AWG-250 kcmil

Configuration

Physical Attribute - Pad Orientation	Straight
Physical Attribute - Pad Configuration	1.50 x 3 - 2 holes
Physical Attribute - Pad Alignment	Offset
Physical Attribute - Number of Holes	2
Connector Type	Terminal

Dimensions

Dimension - Pad Width inch	1.50 in
Package Height	0.000 in
Dimension - Height mm	45.7 mm
Dimension - Hole Size fraction	9/16
Dimension - Height inch	1.80 in
Package Weight	0.000 lb.
Package Length	0.000 in
Dimension - F Width Center to Center inch	1.75 in
Package Width	0.000 in
Dimension - L Length Overall mm	143 mm
Dimension - Width mm	51 mm
Dimension - Width inch	2.00 in
Dimension - B Length inch	2.38 in
Dimension - D inch	3.00 in
Dimension - N inch	0.62 in
Dimension - Length Overall inch	5.62 in

General

Material - Hardware	DURIUM™ Silicon Bronze
One Wrench Installation	Y
Plated	Y
Clamping Element Design	Body And Cap
UPC	781810174166
Material	Copper Alloy
Plating Type	Tin - Electro Plated
UPC 12 Digit	781810174166
UPC 14 Digit GTIN	00781810174166

Logistics

Pallet Quantity	1
Carton Quantity	1



A Hubbell brand

Product Assets

[Catalog \[English\]](#)