


Substation - Copper Terminal

By Burndy

Catalog # [NAS2934N](#)

Cast Cu Alloy Reversible Cap Terminal, Bolted, #6 Sol - 250 kcmil
Cu Cable, 4-NEMA Pad Holes, Silicon Bronze H/W, .56" Hole Dia



Application

Substation

Specifications

Certification - UL Recognized	No
Certification - cULus	No
Certification - ETL	No
Standards - RoHS Compliance Status	EX
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Large Groove Min	2/0 str
Conductor - Large Groove Max	250 kcmil
Conductor - Copper Str Size	6 AWG 5 AWG 4 AWG 3 AWG 2 AWG 1 AWG 1/0 2/0 AWG 3/0 AWG 4/0 AWG 250 kcmil
Conductor - Small Groove Min	6 sol
Conductor - Small Groove Max	1/0 str
Conductor - Copper Solid Size	6 AWG 5 AWG 4 AWG 3 AWG 2 AWG 1 AWG 1/0 AWG 2/0 AWG 3/0 AWG 4/0 AWG
Number Of Conductors	1
Conductor - Connection Combination	Cable to Flat
Conductor - Copper Solid Size Range	6 AWG-4/0 AWG
Conductor Type	- CU C Str-Size - CU C Solid-Size

Conductor - Copper Str Size Range 6 AWG-250 kcmil

Configuration

Physical Attribute - Pad Orientation	Straight
Physical Attribute - Pad Configuration	3 x 3 - 4 holes
Physical Attribute - Pad Alignment	Offset
Physical Attribute - Number of Holes	4
Connector Type	Terminal

Dimensions

Dimension - Pad Width inch	3.00 in
Package Height	0.000 in
Dimension - Height mm	45.7 mm
Dimension - Hole Size fraction	9/16
Dimension - Height inch	1.80 in
Dimension - Height fraction	1-4/5 in
Package Weight	0.000 lb.
Package Length	0.000 in
Dimension - F Width Center to Center inch	1.75 in
Package Width	0.000 in
Dimension - L Length Overall mm	143 mm
Dimension - Width mm	51 mm
Dimension - Width inch	2.00 in
Dimension - B Length inch	2.38 in
Dimension - D inch	3.00 in
Dimension - N inch	0.62 in
Dimension - Length Overall inch	5.62 in

General

Material - Hardware	DURIUM™ Silicon Bronze
One Wrench Installation	Y
Plated	N
Clamping Element Design	Body And Cap
UPC	781810002193
Material	Copper Alloy
Plating Type	Unplated
UPC 12 Digit	781810002193
UPC 14 Digit GTIN	00781810002193

Logistics

Pallet Quantity	216
Carton Quantity	6



A Hubbell brand

Product Assets

[Catalog \[English\]](#)