


Substation - Copper Terminal

By Burndy

Catalog # [NAS3434NTN](#)

Substation Connectors



Application

Substation

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	EX
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Solid Size	1/0 AWG 2/0 AWG 3/0 AWG 4/0 AWG
Conductor - Large Groove Min	250 kcmil
Conductor - Large Groove Max	500 kcmil
Number Of Conductors	1
Conductor - Connection Combination	Cable to Flat
Conductor - Copper Solid Size Range	1/0 AWG-4/0 AWG
Conductor Type	- CU C Str-Size - CU C Solid-Size
Conductor - Copper Str Size Range	1/0 -500 kcmil
Conductor - Copper Str Size	1/0 2/0 AWG 3/0 AWG 4/0 AWG 250 kcmil 300 kcmil 350 kcmil 400 kcmil 450 kcmil 500 kcmil
Conductor - Small Groove Min	1/0 sol
Conductor - Small Groove Max	4/0 str

Configuration

Physical Attribute - Pad Orientation	Straight
--------------------------------------	----------

Physical Attribute - Pad Configuration	3 x 3 - 4 holes
Physical Attribute - Pad Alignment	Offset
Physical Attribute - Number of Holes	4
Connector Type	Terminal

Dimensions

Dimension - Pad Width inch	3.00 in
Package Height	0.000 in
Dimension - Height mm	52.1 mm
Dimension - Hole Size fraction	9/16
Dimension - Height inch	2.05 in
Package Weight	0.000 lb.
Dimension - Width mm	56 mm
Dimension - Width inch	2.20 in
Package Length	0.000 in
Dimension - F Width Center to Center inch	1.75 in
Package Width	0.000 in
Dimension - L Length Overall mm	143 mm
Dimension - B Length inch	2.38 in
Dimension - D inch	3.00 in
Dimension - N inch	0.62 in
Dimension - Length Overall inch	5.62 in

General

Plated	Y
Material - Hardware	DURIUM™ Silicon Bronze
One Wrench Installation	Y
Clamping Element Design	Body And Cap
UPC	781810118474
Material	Copper Alloy
Plating Type	Tin - Electro Plated
UPC 12 Digit	781810118474
UPC 14 Digit GTIN	00781810118474

Logistics

Pallet Quantity	1
Carton Quantity	1



A Hubbell brand