




Substation - Aluminum Bolted Terminal

By Burndy

Catalog # [NAR36A44N](#)

Substation Connectors



Application

Substation

Conductor - ACSR Str Size Range336.4 (18/1) Merlin kcmil-477. (30/7) Hen kcmil

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	EX
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Size	350 kcmil 397 kcmil 400 kcmil 450 kcmil 477 kcmil 500 kcmil 550 kcmil 556 kcmil 600 kcmil
Conductor - AL Str Size Range	350 kcmil-600 kcmil
Conductor Type	- AL C Str-Size - ACSR C Str-Size
Conductor - ACSR Str Size	336.4 (18/1) Merlin kcmil 336.4 (26/7) Linnet kcmil 336.4 (30/7) Oriole kcmil 397.5 (18/1) Chickadee kcmil 397.5 (24/7) Brant kcmil 397.5 (26/7) Ibis kcmil 397.5 (30/7) Larkspur kcmil 477.0 (18/1) Pelican kcmil 477.0 (24/7) Flicker kcmil 477.0 (26/7) Hawk kcmil 477. (30/7) Hen kcmil
Conductor - Copper Str Size Range	350 kcmil-600 kcmil
Conductor - Copper Str Size	350 kcmil 400 kcmil 450 kcmil 500 kcmil 550 kcmil 600 kcmil

Configuration

Physical Attribute - Pad Orientation	Straight
Physical Attribute - Pad Configuration	4 x 4 - 4 holes
Connector Type	Terminal

Dimensions

Dimension - Pad Width inch	4.00 in
Package Height	0.000 in
Dimension - Height mm	66.5 mm
Dimension - Height inch	2.62 in
Package Weight	0.000 lb.
Dimension - Width mm	70 mm
Dimension - Width inch	2.74 in
Package Length	0.000 in
Dimension - F Width Center to Center inch	1.75 in
Package Width	0.000 in
Dimension - L Length Overall mm	199 mm
Dimension - B Length inch	3.38 in
Dimension - D inch	4.00 in
Dimension - N inch	1.12 in
Dimension - Length Overall inch	7.82 in

General

Plated	N
Material - Hardware	Aluminum
UPC	781810369784
Material	Aluminum Alloy
Plating Type	Unplated
UPC 12 Digit	781810369784
UPC 14 Digit GTIN	00781810369784

Logistics

Pallet Quantity	1
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)