


Substation - Copper Terminal

By Burndy
Catalog # [NAS292N90](#)

Substation Connectors



Application

Substation

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	EX
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Solid Size	6 AWG 5 AWG 4 AWG 3 AWG 2 AWG 1 AWG 1/0 AWG 2/0 AWG 3/0 AWG 4/0 AWG
Conductor - Large Groove Min	2/0 str
Conductor - Large Groove Max	250 kcmil
Number Of Conductors	1
Conductor - Connection Combination	Cable to Flat
Conductor - Copper Solid Size Range	6 AWG-4/0 AWG
Conductor Type	- CU C Str-Size - CU C Solid-Size
Conductor - Copper Str Size Range	6 AWG-250 kcmil
Conductor - Copper Str Size	6 AWG 5 AWG 4 AWG 3 AWG 2 AWG 1 AWG 1/0 2/0 AWG 3/0 AWG 4/0 AWG 250 kcmil

Conductor - Small Groove Min	6 sol
Conductor - Small Groove Max	1/0 str

Configuration

Physical Attribute - Pad Orientation	90 Degree
Physical Attribute - Pad Configuration	1.50 x 3 - 2 holes
Physical Attribute - Pad Alignment	Offset
Physical Attribute - Number of Holes	2
Connector Type	Terminal

Dimensions

Dimension - Pad Width inch	1.50 in
Package Height	0.000 in
Dimension - Height mm	122.2 mm
Dimension - Hole Size fraction	9/16
Dimension - Height inch	4.81 in
Package Weight	0.000 lb.
Dimension - Width mm	51 mm
Dimension - Width inch	2.00 in
Package Length	0.000 in
Dimension - F Width Center to Center inch	1.75 in
Package Width	0.000 in
Dimension - L Length Overall mm	122 mm
Dimension - B Length inch	2.38 in
Dimension - D inch	3.00 in
Dimension - N inch	0.62 in
Dimension - Length Overall inch	4.81 in

General

Plated	N
Material - Hardware	DURIUM™ Silicon Bronze
One Wrench Installation	Y
Clamping Element Design	Body And Cap
UPC	781810077450
Material	Copper Alloy
Plating Type	Unplated
UPC 12 Digit	781810077450
UPC 14 Digit GTIN	00781810077450

Logistics

Pallet Quantity	1
Carton Quantity	10



A Hubbell brand

Product Assets

[Catalog \[English\]](#)