


Substation - Copper Terminal

By Burndy

Catalog # [NAS4034N](#)

Cast Cu Alloy Reversible Cap Terminal, Bolted, 2/0 Str - 800 kcmil Cu Cable, 4-NEMA Pad Holes, Silicon Bronze H/W, .56" Hole Dia, 5.88 L, 0.31 T, 2.44 W



Application

Substation

Specifications

Certification - UL Recognized	No
Certification - cULus	No
Certification - ETL	No
Standards - RoHS Compliance Status	EX
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Large Groove Min	500 kcmil
Conductor - Large Groove Max	800 kcmil
Conductor - Copper Str Size	2/0 AWG 3/0 AWG 4/0 AWG 250 kcmil 300 kcmil 350 kcmil 400 kcmil 450 kcmil 500 kcmil 550 kcmil 600 kcmil 700 kcmil 750 kcmil 800 kcmil
Conductor - Small Groove Min	2/0 str
Conductor - Small Groove Max	500 kcmil
Conductor - Copper Solid Size	2/0 AWG 3/0 AWG 4/0 AWG
Number Of Conductors	1
Conductor - Connection Combination	Cable to Flat
Conductor - Copper Solid Size Range	2/0 AWG-4/0 AWG
Conductor Type	- CU C Str-Size - CU C Solid-Size
Conductor - Copper Str Size Range	2/0 AWG-800 kcmil

Configuration

Physical Attribute - Pad Orientation	Straight
Physical Attribute - Pad Configuration	3 x 3 - 4 holes
Physical Attribute - Pad Alignment	Offset
Physical Attribute - Number of Holes	4
Connector Type	Terminal

Dimensions

Dimension - Pad Width inch	3.00 in
Package Height	0.000 in
Dimension - Height mm	58.4 mm
Dimension - Hole Size fraction	9/16
Dimension - Height inch	2.30 in
Dimension - Height fraction	2-3/10 in
Package Weight	0.000 lb.
Package Length	0.000 in
Dimension - F Width Center to Center inch	1.75 in
Package Width	0.000 in
Dimension - L Length Overall mm	149 mm
Dimension - Width fraction	2-11/25 in
Dimension - B Length fraction	2-31/50 in
Dimension - Width mm	62 mm
Dimension - Width inch	2.44 in
Dimension - B Length inch	2.62 in
Dimension - D inch	3.00 in
Dimension - N inch	0.62 in
Dimension - Length Overall inch	5.88 in

General

Material - Hardware	DURIUM™ Silicon Bronze
One Wrench Installation	Y
Plated	N
Clamping Element Design	Body And Cap
UPC	781810002865
Material	Copper Alloy
Plating Type	Unplated
UPC 12 Digit	781810002865
UPC 14 Digit GTIN	00781810002865

Logistics

Pallet Quantity 720
Carton Quantity 4

Product Assets

[Catalog \[English\]](#)



A Hubbell brand