




**NHNT1644, Substation Copper T
Connector, 90 Degrees, Tube to Cable, 1-
1/4" IPS/EHPS Run, 4/0 AWG-1000 kcmil
Tap, 230kV**

By Burndy

Catalog # [NHNT1644](#)

Substation T Connectors



Features

- Type NHNT for Copper Tube to Cable T Application
- High copper alloy reversible T-Connector for joining a wide range of run pipe and tap cables
- One-wrench installation

Application

Substation

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	EX
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Connection Combination	Tube to Cable
Conductor Type	• CU Tube Std-Run • CU C Str-Run • CU C Solid-Run • CU C Str-Tap • CU C Solid-Tap
Conductor - Copper Str Tap Range	4/0 AWG-1000 kcmil
Conductor - Copper Str Tap	• 4/0 AWG • 250 kcmil • 300 kcmil • 350 kcmil • 400 kcmil • 450 kcmil • 500 kcmil • 550 kcmil • 600 kcmil • 700 kcmil • 750 kcmil • 800 kcmil • 850 kcmil • 900 kcmil • 1000 kcmil

Conductor - Copper Tube Std Run Range	1 1/4 IPS
Conductor - Copper Tube Std Run	1 1/4 IPS

Configuration

Physical Attribute - Number of Tap Conductors	1
Physical Attribute - Number of Run Conductors	1
Connector Type	T-Connector

Dimensions

Dimension - Height mm	68.3 mm
Dimension - Height inch	2.69 in
Dimension - Height fraction	2-69/100 in
Dimension - B Length fraction	2-69/100 in
Dimension - Width mm	74 mm
Dimension - Width inch	2.90 in
Dimension - L Length Overall mm	167 mm
Dimension - B Length inch	2.69 in
Dimension - Width fraction	2-9/10 in
Dimension - Length BB inch	2.88 in
Dimension - Length Overall inch	6.58 in

Force Related

Installation Torque Recommended in-lb	480 lb-in
---------------------------------------	-----------

General

Plated	N
Material - Hardware	DURIUM™ Silicon Bronze
One Wrench Installation	Y
UPC	781810002391
Type	Tube to Cable Couplers
Material	Copper Alloy, Cast
Plating Type	Unplated
UPC 12 Digit	781810002391
UPC 14 Digit GTIN	00781810002391

Product Assets

[Catalog \[English\]](#)



A Hubbell brand