



NHNT3434, Substation Copper T Connector, 90 Degrees, Cable to Cable, 1/0 Sol-500 kcmil

By Burndy
Catalog # [NHNT3434](#)

Cast Copper alloy T-Connector, 1/0 Sol.-500 kcmil, 4.84 in Length, Cable to Cable

Features

- Cast Copper Alloy T-Connector for Cable to Cable

Application


Substation

Specifications

Certification - UL Recognized	No
Certification - cULus	No
EU RoHS Indicator	Yes
Certification - ETL	No
Standards - RoHS Compliance Status	EX
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Run Range	1/0 -500 kcmil
Conductor - Copper Str Run	• 1/0 • 2/0 AWG • 3/0 AWG • 4/0 AWG • 250 kcmil • 300 kcmil • 350 kcmil • 400 kcmil • 450 kcmil • 500 kcmil
Conductor - Copper Solid Run Range	2/0 AWG-4/0 AWG
Conductor - Copper Solid Run	• 2/0 AWG • 3/0 AWG • 4/0 AWG
Conductor - Connection Combination	Cable to Cable
Conductor - Copper Solid Tap Range	2/0 AWG-4/0 AWG
Conductor - Copper Solid Tap	• 2/0 AWG • 3/0 AWG • 4/0 AWG
Conductor Type	• CU Tube Std-Run • CU C Str-Run • CU C Solid-Run



Conductor - Copper Str Tap Range	• CU C Str-Tap • CU C Solid-Tap
Conductor - Copper Str Tap	1/0 -500 kcmil
	• 1/0 • 2/0 AWG • 3/0 AWG • 4/0 AWG • 250 kcmil • 300 kcmil • 350 kcmil • 400 kcmil • 450 kcmil • 500 kcmil

Configuration

Physical Attribute - Number of Tap Conductors	1
Physical Attribute - Number of Run Conductors	1
Connector Type	T-Connector

Dimensions

Package Height	0.000 in
Dimension - Height mm	58.9 mm
Dimension - Height inch	2.32 in
Dimension - Height fraction	2-8/25 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	137 mm
Dimension - Width fraction	2-14/25 in
Dimension - B Length fraction	2-31/50 in
Dimension - Width mm	65 mm
Dimension - Width inch	2.56 in
Dimension - B Length inch	2.62 in
Dimension - Length BB inch	2.62 in
Dimension - Length Overall inch	5.38 in

Force Related

Installation Torque Recommended in-lb	480 lb-in
---------------------------------------	-----------

General

Material - Hardware	DURIUM™ Silicon Bronze
One Wrench Installation	Y
Plated	N
Sub Brand	T-CONNECTOR
UPC	781810002230
Type	Tube to Cable Couplers
Material	Copper Alloy, Cast
Plating Type	Unplated



A Hubbell brand

UPC 12 Digit	781810002230
UPC 14 Digit GTIN	00781810002230

Logistics

Pallet Quantity	1
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)