



PATRIOT® Series, T3 Technology 15-Ton Battery Crimper, C-Head, Uncovered, two 5.0Ah 18V Li-Ion Batteries, 12V-DC Charger, Nylon Pro Bag

By Burndy  
Catalog # PAT46T3SU05D3

T3 Tech 15-Ton C-Head, 5Ah, DC, PB

Features

- TRACK crimp locations with onboard GPS - BURNDY Exclusive!
- TRACE individual crimps with comments and output force validation
- TRANSMIT via Bluetooth® technology and sync data to the cloud
- C-head with 2" jaw opening with 355° head rotation
- Uses P Dies and U Dies with PUADP1 Adapter
- Bright LED worklight and Red/Green LED to validate output force
- Improved ergonomic design with more balance and better grip to reduce user fatigue
- Accepts 2.0Ah-6.0Ah Makita Lithium-ion Batteries

Application

Crimping

Conductor

|                 |                                                                                                                                                                    |
|-----------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Crimping Ranges | <ul style="list-style-type: none"><li>• Copper: #14 AWG Str. - 1500 kcmil</li><li>• Aluminum: #8 AWG - 1250 kcmil</li><li>• Ground Rod: 1/2"-1" diameter</li></ul> |
|-----------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------|

Current

|                   |        |
|-------------------|--------|
| Operating Voltage | 18 VDC |
|-------------------|--------|

Dimensions

|        |           |
|--------|-----------|
| Weight | 18.15 lb. |
| Height | 14.13 in  |
| Width  | 3.26 in   |



|            |                               |
|------------|-------------------------------|
| Length     | 18.44 in                      |
| Dimensions | 18.44 in x 3.26 in x 14.13 in |

Force Related

|                      |        |
|----------------------|--------|
| Crimp Force Capacity | 15 ton |
|----------------------|--------|

General

|                          |                                              |
|--------------------------|----------------------------------------------|
| Tool Type                | Battery Actuated Crimper, T3 Technology      |
| Container Type           | Nylon Pro Bag                                |
| Application - For Use On | Copper, Aluminum, ACSR Terminals and Splices |
| Die Type                 | P Die and U Die with PUADP1 Adapter          |
| UPC                      | 621945625563                                 |
| Type                     | Crimper                                      |
| Sub Brand                | PATRIOT®                                     |
| Series                   | PATRIOT® Series                              |

Logistics

|                  |                                                         |
|------------------|---------------------------------------------------------|
| Pallet Quantity  | 12                                                      |
| Carton Quantity  | 1                                                       |
| Package Contents | Crimper, (2) Batteries, Charger, Lanyard, Nylon Pro Bag |

Operational

|              |                                                            |
|--------------|------------------------------------------------------------|
| Battery Type | 5.0Ah 18V Li-Ion (Accepts 2.0Ah-6.0Ah Makita LI Batteries) |
| Power Source | 12V-DC Charger                                             |

Product Assets

[Catalog \[English\]](#)